

# Lampholders, Starters and Adapters



## Lampholder Accessories

### Incandescent Lampholders, Medium Base



Catalog Number	RL124*	RL124H	RL202
Description	Pigtail medium base socket with 6 inch leads, rubber with #18 gauge wire	Phenolic medium base socket with hook, insulation piercing termination	Medium lampholder to lampholder adapter, pull chain with two 2-prong outlets without ground
Rating	660W 250V	660W 250V	660W 125V 15A 125V

Note: \*cSAus Certified only.

### Incandescent Adapters, Medium Base



Catalog Number	RL150	RL154	RL200	RL201
Description	Medium to medium base extension, screw-in, E26 to E26 socket	Mogul to medium base adapter, screw-in, E39 to E26 socket	Outlet adapter, 2-prong plug to medium lampholder	Medium lampholder adapter, medium lampholder to outlet without ground
Rating	250W 250V	660W 250V	15A 660W 125V, 15A 125V, NEMA 1-15R	15A 125V, NEMA 1-15R

### Lamp Switches



Catalog Number	RL120	RL121	RL122	RL125
Description	Pull chain switch, 2 circuit, L1/L2/L1+L2/OFF	Pull chain switch, SPST ON/OFF	Pull chain switch, L1/L2/L3/OFF	Rotary switch, SPST ON/OFF
Rating	6A 125V AC, 3A 250V AC, 3A 125V "L"	6A 125V AC, 3A 250V AC, 3A 125V "L"	6A 125V AC, 3A 250V AC	6A 125V AC, 3A 250V AC, 3A 125V "L"

Note: 6 inch wire leads are #18 AWG AWM/TEW 105°C 600V.

### Snap-in Receptacles



Catalog Number	RR374	RR374W
Description	Single receptacle, black	Single receptacle, white
Rating	15A 125V, 3-wire NEMA 5-15R	15A 125V, 3-wire NEMA 5-15R

- Accommodate panel thickness of .031 to .062 inch (0.7 to 1.5 mm)
- Panel cutout .95 x .95 inch (24.1 x 24.1 mm)
- #14 AWG 6 inch AWM/TEW FT1 105°C 600V on black and white leads
- #14 AWG 6 inch AWM/TEW FT1 600V on green lead