Switches, Single Pole 15A, 120-277V AC Specification Grade Commercial Switch



Features

- Thread cleaning captive mounting screw
- Abuse resistant nylon toggle
- Steel, zinc plated bridge is corrosion resistant

Ordering Information

DescriptionToggle ColorUPCToggle, back and sideBrown783585153wiredVirentVirent	Catalog Number 3759 CSB115
--	-------------------------------

Listings

UL Listed CSA Certified Fed. Spec. W-S-896

Specifications

•	
Top Material	Thermoplastic, Gray
Base Material	Thermoplastic, Black
Toggle Material	Nylon
Contacts	Silver Alloy
Terminal Screws	Brass
Auto Grounding Mounting Bridge	Zinc Plated Steel
Ground Screw	Brass (Green)

Performance

Electrical

Dielectric Voltage	Withstands 1500V AC minimum for 1 minute
Max. Continuous Current	15A
Max. Working Voltage	277V AC
Overload	Minimum 4.8 times rated current for 100 cycles
Temperature Rise	30°C maximum at rated current

Mechanical

Terminal Accommodations #14 AWG min. - #10 AWG max. solid and stranded copper wire only


Environmental

Flammability	
Operating Temperature	

ature Max. continuous: 75°C; Min. continuous: -40°C without impact

UL 94V-2





Online Resources

Customer Use Drawing eCatalog

