

Straight Blade Devices

Industrial Grade Extra Heavy Duty, Specification Grade Single Receptacles

15A and 20A 125V and 250V Receptacles, Back and Side Wired



Rating	Color	Single		Color	Isolated Ground		Color	Corrosion Resistant
		Standard	Weather Resistant		Standard	Weather Resistant		Standard
NEMA 5-15, 15A 125V 	Black	5261BLK	5261BLKWR	Gray	5261IGGRY	5261IGGRYWR	Yellow	5261CR
	Brown	5261	5261WR	Ivory	5261IGI	5261IGIWR		
	Gray	5261GRY	5261GRYWR	Orange	5261IG	5261IGWR		
	Ivory	5261I	5261IWR	White	5261IGW	5261IGWWR		
	Red	5261RED	5261REDWR					
White	5261W	5261WWR						
NEMA 5-20, 20A 125V 	Black	5361BLK	5361BLKWR	Gray	5361IGGRY	5361IGGRYWR	Yellow	5361CR
	Brown	5361	5361WR	Ivory	5361IGI	5361IGIWR		
	Gray	5361GRY	5361GRYWR	Orange	5361IG	5361IGWR		
	Ivory	5361I	5361IWR	White	5361IGW	5361IGWWR		
	Red	5361RED	5361REDWR					
White	5361W	5361WWR						
NEMA 6-15, 15A 250V 	Black	5661BLK	—				Yellow	—
	Brown	5661	—					
	Gray	5661GRY	—					
	Ivory	5661I	—					
	Red	5661RED	—					
White	5661W	—						
NEMA 6-20, 20A 250V 	Black	5461BLK	—				Yellow	5461CR
	Brown	5461	—					
	Gray	5461GRY	—					
	Ivory	5461I	—					
	Red	5461RED	—					
White	5461W	—						

Notes: See page R-6 for weather resistant description.

See Section C for isolated ground products. See page R-6 for weather resistant description.

See Section I for corrosion-resistant products.

15A and 20A 125V Short Yoke Receptacles



Wiring	Back and Side Wired		Side Wired	
Rating	Color	Standard	Weather Resistant	
NEMA 5-15, 15A 125V	Brown	5284	5284WR	5258
NEMA 5-20, 20A 125V	Brown	—	5384WR	—
NEMA 6-15, 15A 250V	Brown	5684	—	—
NEMA 6-20, 20A 250V	Brown	5484	—	—

15A and 20A 125V Specialty Receptacles



Rating	Description	Color	Catalog Number
NEMA 5-15, 15A 125V	5261 on 4.0" (101.6) round metal box cover	Brown	5281

Product Dimensions Inches (mm)

	Single	Short Yoke	Short Yoke Urea Face
A	4.06" (103.1)	2.25" (57.2)	2.25" (57.2)
B	3.28" (83.3)	1.94" (49.3)	1.75" (44.5)
C	1.38" (35.1)	1.38" (35.1)	1.38" (35.1)
D	0.91" (23.1)	0.81" (20.6)	0.85" (21.6)
E	1.78" (45.2)	1.78" (45.3)	1.49" (37.8)

