



Lineman's Crimping Pliers, 9-Inch



The Lineman's Crimping Pliers feature a crimping die behind the hinge. This provides superior leverage when crimping non-insulated connectors, lugs, and terminals. The rivet on these pliers are closer to the cutting edge which provides 46-Percent more cutting and gripping power than other pliers. Induction hardened cutting knives are extra durable for longer life.

Specifications

Type:	High Leverage Side Cutting/Connector Crimping Pliers	Application:	Cutting and Crimping
Overall Length:	9.33" (23.7 cm)	Material:	Steel
Nose Type:	New England	Jaw Length:	1.594" (4 cm)
Jaw Width:	1.25" (3.2 cm)	Jaw Thickness:	0.625" (1.6 cm)
Jaw Capacity:	1.375" (3.5 cm)	Knife Length:	Yellow
Joint Type:	Locking	Handle Color:	Yellow
Handle Finish:	Plastic-Dipped	Handle Length:	5.563" (14.1 cm)
Insulated:	No	Tether Capable:	No
Weight:	1.0 lb (0.5 kg)		