



Main

Product or component type	Section
---------------------------	---------

Complementary

Fixing mode	Plug-in
System Voltage	600 V AC
[Ie] rated operational current	30 A
Number of poles	3
Busbar description	Ground
Fuse type	H

Environment

product certifications	CSA UL
------------------------	-----------

Offer Sustainability

Green Premium product	Green Premium product
Compliant - since 1438 - Schneider Electric declaration of conformity	Compliant - since 1438 - Schneider Electric declaration of conformity
Reference not containing SVHC above the threshold	Reference not containing SVHC above the threshold
Available	Available
Need no specific recycling operations	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.