



Main

| | |
|-------------------------------|--|
| Range of Product | Harmony XAP |
| Product or Component Type | Die-cast empty control station |
| Device short name | XAPG |
| Product destination | For Ø 22 mm control and signalling units |
| Number of cut-out | 1 cut-out |
| Colour of base of enclosure | Grey RAL 7032) |
| Colour of cover | Grey RAL 7032) |
| Control station type | Metal |
| Material | Die cast zinc |
| Sale per indivisible quantity | 1 |
| IP degree of protection | IP65 IEC 60529 IP657 NF C 20-010 |
| Resistance to chemical agents | Special treatment can be obtained on request |

Complementary

| | |
|---------------------------|--------------------------------|
| Number of vertical rows | 1 |
| Number of horizontal rows | 1 |
| Cut-out dimensions | Ø 22 mm |
| Cable entry | Cable gland 1 x cable gland |
| Thread type | 3/4 NPT |
| CAD overall width | 3.15 in (80 mm) |
| CAD overall height | 3.15 in (80 mm) |
| CAD overall depth | 2.03 in (51.5 mm) |
| Net Weight | 1.16 lb(US) (0.524 kg) |
| Compatibility code | XAPG |

Environment

| | |
|---------------------------------------|--|
| Protective treatment | TH |
| Ambient Air Temperature for Storage | -40...158 °F (-40...70 °C) |
| Ambient air temperature for operation | -13...158 °F (-25...70 °C) |
| Electrical shock protection class | Class I IEC 60536 Class I NF C 20-030 |
| IK degree of protection | IK07 EN/IEC 62262 |

Ordering and shipping details

| | |
|-----------------------|-----------------------|
| Category | 22475 - WALL STATIONS |
| Discount Schedule | CS2 |
| GTIN | 3389118381926 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 18.69 oz (530 g) |
| Returnability | Yes |
| Country of origin | MA |

Packing Units

| | |
|------------------------------|-------------------------|
| Unit Type of Package 1 | PCE |
| Package 1 Height | 3.54 in (9 cm) |
| Package 1 width | 3.39 in (8.6 cm) |
| Package 1 Length | 3.54 in (9 cm) |
| Unit Type of Package 2 | S02 |
| Number of Units in Package 2 | 12 |
| Package 2 Weight | 14.68 lb(US) (6.659 kg) |
| Package 2 Height | 5.91 in (15 cm) |
| Package 2 width | 11.81 in (30 cm) |
| Package 2 Length | 15.75 in (40 cm) |

Offer Sustainability

| | |
|----------------------------|--|
| Sustainable offer status | Green Premium product |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End Of Life Information |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|