


M-8389 3



LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
TOP COVER	VALOX	SEE CHART
BASE	RYNITE	SEE CHART
BRIDGE	.050 BRASS	NICKEL PLATE
LEAD WIRE	#12 COPPER	WHITE/BLACK
CONTACT	.031 BRASS	SILVER PLT
GROUND SPRING	.010 SSTL	
HX HD BD SCREW	BRASS	GREEN
WASHER	.031 FIBER	RED
TRI DRV SCREW	STEEL	ZINC PLATE
CENTER RIVET	SIL BRONZE	

DIMENSION SHEET FOR CAT. NO.

SEE TABLE

REPAIRABLE

NON-REPAIRABLE

B

M-8389

3

BLANK CIRCUIT
I.D. LABEL
1.25 X .37
[31.7 X 9.4]

CAT. NO.	COLOR	CONFIGURATION	RATING
HBL8200SGA	BROWN	 NEMA 5-15R	15A 125V
HBL8200SGIA	IVORY		
HBL8200SGGYA	GRAY		
HBL8200SGRA	RED		
HBL8200SGWA	WHITE		
HBL8200SGALA	ALMOND		
HBL8300SGA	BROWN	 NEMA 5-20R	20A 125V
HBL8300SGIA	IVORY		
HBL8300SGGYA	GRAY		
HBL8300SGRA	RED		
HBL8300SGWA	WHITE		
HBL8300SGALA	ALMOND		

NOTES: INCHES
[MM]

3	ADDED ALMOND CAT. NO'S PER DCN 11596 RCM	MJL	3-31-04
2	ADDED MADE IN KOREA, MM'S PER DCN. 8194-1 TJV	SM	1/15-02
1	INITIAL RELEASE PER DCN#8194	PAC	11-22-00
SYM	REVISIONS	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
HUBBELL HOSPITAL GRADE
15/20A TAMPER RESISTANT
SAFETY RECEPTACLE

TOLERANCES UNLESS OTHERWISE SPECIFIED		WIRING DEVICE-KELLEMS HUBBELL INCORPORATED BRIDGEPORT, CT	
FRACTIONS	±1/64	DR. BY	PAC
DECIMALS	±.005	TR. BY	SCALE 1-2
ANGLES	±2°	CHK'D BY	DATE 11-21-00