


Protect It! 6-Outlet Home Computer Surge Protector, 2-ft. Cord, 180 Joules

MODEL NUMBER: TLP602



Highlights

- 6 outlets / 2-ft. cord
- 180 joule rating

Package Includes

- TLP602 Surge Suppressor
- Instruction manual and warranty information

Description

Tripp Lite's TLP602 offers economical AC surge suppression for workstations, desktop PCs, telecom systems and other sensitive electronics. Built-in AC surge suppression shields connected equipment from damage and performance problems due to transient surges. TLP602 offers 6 total outlets, 2 foot cord. AC suppression rated at 180 joules shields equipment from surges and line noise. Attractive gray housing with keyhole mounting tabs and 1 designated transformer plug outlet offers convenient protection of desktop computer equipment and accessories.

PLUG/OUTLETS: Input: NEMA5-15P/Output: 6 NEMA5-15R/2-ft. AC line cord

ELECTRICAL: 120V AC, 50/60Hz, 15A (Requires NEMA5-15R wall receptacle)

FORMAT: Corded multi-outlet strip

SUPPRESSION: AC: 150V RMS Clamping/180 joules

Features

- 6 outlets
- 2-ft. cord
- Surge suppression rating: 180 joules
- 15 amp resettable circuit breaker
- Includes full normal mode (H-N) and common mode (N-G/H-G) line surge suppression
- Can accommodate 1 large transformer plug without covering remaining outlets, 4 total transformers
- Keyhole support for wall mounting
- Lighted power switch
- \$2,500 Ultimate Lifetime Insurance (USA and Canada Only)

Specifications

OVERVIEW	
UPC Code	037332095404



OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(6) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(2) Yes
Outlet Orientation	Single row
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Voltage Compatibility (VAC)	120
Maximum Surge Amps	12000
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	2
Right-Angle Plug	No
Input Cord Length (m)	0.61
Integrated Cord Clip	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	No
Switches	Combination AC circuit breaker and 2 position on/off power switch
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	180
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	150
UL1449 Let Through Rating	500V
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

PHYSICAL	
Anti-Microbial Protected	No
Color	Light Gray
Color (AC Line Cord)	Light Gray
Housing Color	Light Gray
Integrated Keyhole Mounting Slots	Yes
Keyhole Slot Mounting Measurement (Center to Center)	Distance between slots = 101mm; Distance between slot height = 28mm
Material of Construction	Plastic
Outlets Measurement (Center to Center)	28.5mm
Receptacle Color	Light gray
Shipping Dimensions (hwd / cm)	5.08 x 10.16 x 28.45
Shipping Dimensions (hwd / in.)	2.00 x 4.00 x 11.20
Shipping Weight (kg)	0.32
Shipping Weight (lbs.)	0.70
Unit Dimensions (hwd / cm)	3.00 x 4.29 x 23.98
Unit Dimensions (hwd / in.)	1.18 x 1.69 x 9.44
Unit Weight (kg)	0.26
Unit Weight (lbs.)	.57
SPECIAL FEATURES	
Rotatable Outlets	No
CERTIFICATIONS	
UL1449 3rd Edition (AC Suppression)	UL1449 3RD EDITION
UL1363 (Power Tap)	UL1363
Canada	cUL
Approvals	Exceeds IEEE 587 category A&B specifications
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$2,500 Ultimate Lifetime Insurance

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>