
Little GIANT.

TE-5.5-MD-HC



Features

- Thermally protected, totally enclosed, fan cooled, split phase motor
- Ball bearings
- Conduit box (Must be field wired cord not included)
- Specific gravity to 1.1
- Fluid temperature to 180°F
- Ambient air temperature to 77°F
- Run-dry capability up to 8 hours

NOTE: Consult your local distributor or the factory for applications with higher ambient temperatures, specific gravities and viscosities.


Construction

- Volute Glass-filled Ryton[®]
- Backplate Glass-filled Ryton[®]
- Impeller Glass-filled Ryton[®] with carbon bushing
- Shaft Ceramic
- Thrust Washers Ceramic
- O-Ring Viton[®]

The Little Giant MD-HC series features leakproof, seal-less magnetic drives and are designed for in-line, nonsubmersible use. Volute, magnet housing and impeller are glass-filled Ryton[®] for excellent chemical resistance. Ceramic shaft and thrust washers are 99.5% pure alumina for excellent wear and reliable service. Pumping heads are easily rotated, cleaned or serviced. Spindle shaft is supported at both ends to prevent impeller damage during start-up and stop of pump.

 $Ryton^{\circledast}$ is a registered trademark of Chevron Phillips Chemical Company $Viton^{\circledast}$ is a registered trademark of DuPont Performance Elastomers


TE-5.5-MD-HC




NOTE: Designs and dimensions may vary for various reasons (i.e. type of motor). This information should be used as general guide rather than an unqualified guarantee. Specifications are subject to change without prior notice.

Specifications

Model	Model Item Intake Discharge									Performance (GPM @ Head)					Shut Off		Power	Weight
No.	No.	Size	Size	Listing(s)	HP	Volts	Hertz	Amps	Watts	5'	10'	20'	30'	40'	Feet	PSI	Cord (ft.)	(lbs.)
TE-5.5-MD-HC	585604	1" FNPT	3/4" MNPT	UR/C-CSA	1/3	115	50/60	5.6/5.0	340/525	32	30	26	19	6	40.5	17.5	N/A	28.00
						230	50/60	2.8/2.5	340/525									
TE-5.5-MD-HC	585698	1" FNPT	3/4" MNPT		Pump	head les	s motor											7.00





Replacement Parts

ITEM	PART NO.	DESCRIPTION					
А	185112	Volute					
В	187085	Thrust Washer					
С	185100	Shaft					
D	185138	Impeller/Bushing					
E	924016	O-Ring					
F	185181	Backplate					
1	903712	Bolt					
2	921050	Washer					
3	185172	Drive Magnet					
4	185162	Magnet Housing					
NOTE: Barta A E contract fluid							

NOTE: Parts A-F contact fluid



O Box 12010 • Oklahoma City, OK 73157 Phone: 800.701.7894 • Fax: 800.701.8046 E-mail: customerservice@littlegiant.com