



Mfg.#	A	B	C	D
4TLP4	.680"	.800"	2.610"	.383"
4TLP5	.965"	1.300"	2.925"	.470"
4TLP6	1.515"	1.844"	2.965"	.535"
4TLP7	2.000"	2.340"	3.050"	.655"

Breaking Strength 120,. 200,. 225 and 240 Lbs.
 Side Squeeze Buckles Dim. + or- .005"