



NOBLES[®]
ENGINEERED BY TENNANT COMPANY

SPEED SCRUB[®] 15 inch 3 gallon walk-behind micro scrubber



- Get deep cleaning results in places you couldn't scrub before
- Excellent recovery of dirty water thanks to the expertly engineered, high-powered recovery system
- Start cleaning immediately with the simple "all-in-one" trigger operation

**Built to be tough.
Made to be easy.**

Small, ultra low-profile cylindrical scrubber



Get the job done right the first time, everytime! The Speed Scrub 15" corded scrubber is the best choice for smaller jobs.

Clean deep

Remove even the toughest grime with the cylindrical brush system's 33 lb / 15 kg of focused down pressure and 1,200 rpm brush speed.

Complete water recovery

Excellent pick up of dirty water with the no-hassle squeegee system and powerful 1.2 hp / 0.89 kW vacuum that pulls 86 in / 2180 mm of water lift.

Extremely reliable

Expect years of dependable operation thanks to the category's only cast aluminum frame and scrub head and industry-leading 10 / 3 / 3 warranty.



Engineered by Tennant Company, the Speed Scrub 15 is the smart, reliable choice for your no-nonsense cleaning needs.

Nobles

701 North Lilac Drive
Minneapolis, MN 55422

USA/Canada: +1.800.553.8033
Quebec: +1.800.361.9050

www.nobles.com
nobles@tennantco.com

Speed Scrub Specifications

Applications: Food processing areas and kitchens, convenience stores, quick-serve restaurants, swimming pool decks, locker rooms, and many other small spaces.

Cleaning path width	15 in / 380 mm
Solution tank	3 gal / 11.4 L
Solution flow rate	0.1 gpm / 0.38 L/min
Down pressure	33 lb / 15 kg
Recovery tank	4.5 gal / 17 L
Water lift	86 in / 2,180 mm
Sound level (operator ear)	72 dBA
Power cord	50 ft / 15 m

Warranty See your local representative for warranty information.