

# High Speed Burnisher with Dust Control



## Get superior gloss performance with our high speed dust control burnisher.

Use this burnisher once and you'll know what everyone's talking about. The flexible dust skirt provides excellent dust control. In fact, there's no need to dust mop after using.

### Easy to use

Reduce training time with easy-to-use controls such as the Insta-Adjust™ handle, which allows operator's to adjust instantly while burnishing. Transporting and storage of the unit is convenient with the Insta-Adjust™ handle, which folds forward when not in use.

### Rugged and quiet

Durable polyethylene construction, low vibration and 66 dBA sound level ensures a high quality burnisher.



## Key Benefits

- Consistent results on uneven floors with the patented free-floating head
- Excellent gloss results with powerful 2,000 rpm “on the floor” pad rotation
- Variable pad pressure from 15-45 lb / 7-20 kg for ultimate finish performance



# High Speed Burnisher with Dust Control



Features	Specifications*
<b>Product Name</b>	BR-2000-DC
<b>Pad Drive System</b> Pad speed burnishing Motor volts Motor HP Motor type Pad diameter Motor amps Pad drive description Pad pressure	2000 rpm @ full load (15 amps) 120 V 1.5 hp / 1.12 kW Direct drive, permanent magnet DC, circuit breaker protected 20 in / 510 mm 15 A Flexible disk with centering lock, free floating, accommodates uneven floors Adjustable 15-45 lb / 7-20 kg
<b>Debris Recovery System</b> Dust control system Filter description	Built-in dust collection system with flexible dust skirt Cloth filter bag (standard), filters w/ 99.9% efficiency at 0.3 micron
<b>Productivity</b> Max. coverage (per hour)	10000 ft <sup>2</sup> / 929m <sup>2</sup>
<b>Dimensions/Weight/Sound level</b> Length Width Height Net weight Sound level (operator's ears)	31.5 in / 800 mm 22.5 in / 570 mm 47 in / 1190 mm 92 lb / 42 kg 66 dBA
<b>Power Cord</b> Power cord length Power cord type	75 ft / 23 m 14 gauge, 3-wire, ST-Safety yellow cord
<b>Approvals</b>	CSA , ETL
<b>Warranty</b>	See your sales representative or authorized distributor for complete warranty details.

\*Specifications subject to change without notice