

RB1224

Relay Module

Description

Altronix RB1224 Relay Module can be utilized in many different applications such as: Dry Contact, Line Seizure, Polarity Reversal, Latching Dry Contact, and much more. RB1224 is Snap Track mountable.



RB1224

Specifications

Input

Voltage	12VDC or 24VDC operation.
Current Draw	75mA.

Contact Rating

5A/220VAC or 28VDC DPDT contacts.

Indicators (LED)

Trigger	Relay is triggered. Remote LED status output.
---------	--

Physical and Environmental

Dimensions (L x W x H)

2.75" x 2" x 1" (69.85mm x 50.08mm x 25.4mm).

Product Weight 0.15 lb. (0.06 kg).

Shipping Weight 0.25 lb. (0.11 kg).

Temperature

Operating -25°C to 55°C (-13°F to 131°F).

Storage -25°C to 70°C (-13°F to 158°F).

Relative Humidity 85% +/-5%.