



4YU32 - Motor Spec Sheet



Part Detail

Agency Compliance	UL Listed, CSA Certified
Motor Type	Shaded Pole
Motor Enclosure	Vented
NEMA Frame Size	Nonstandard
Motor Insulation	B
Horsepower (Typ.)	1/30 hp
Voltage	115
Full Load Amps	1.3/0.92/0.68
RPM	1,550 rpm, 1,300 rpm, 1,050 rpm
Nominal Efficiency	27 %
Hertz (Cycle)	60 Hz
Motor Phase	1