

# NYLON CONVERTIBLE TRUCK

## Dayton Model 4ZJ32

- Made of Lightweight rust-proof fiberglass reinforced nylon polymer
- One piece frame which is fully integrated for increased rigidity and durability
- Contoured cross straps designed to cradle a variety of objects
- Built in stairclimbers for easy glide over curbs and stairs
- 10" pneumatic tires help cushion the load over uneven surfaces
- Converts from 2 wheel Vertical position to 4 wheel Horizontal position

Load Capacity: 600 lbs.

Frame: 1-Piece Molded Frame

Handle Style: Flow Back

Overall Height: 50"

Overall Width: 21"

Toe Plate: 7" x 15"

Wheels: 10" Pneumatic Tires with Welded Steel Hubs and 5/8" Ball Bearings

Shipping Weight: 31 lbs.

