



CDR-2CFB Double Cast Iron Space Saver Hot Plate Space saving front-to-back design

7-1/2" cast iron elements 900W/burner / 1,800W total / 120V Infinite Heat Controls

Made in America

CDR-2C Double Cast Iron Hot Plate 7-1/2" cast iron elements 900W/burner / 1,800W total / 120V



CSR-1CH Hi-power Single Cast Iron Hot Plate 7-1/2" cast iron element 1500W / 120V

All Models: • Cast Iron Elements • Heavy Duty Stainless Construction

Also Available

Made in Germany



KR-1: Cast Iron Hot Plate (Same as KR-S2, except Black Enamel Finish)



KR-S2: Cast Iron Hot Plate 7-1/8" element / 1500W / 120V

COMMON FEATURES

- Heavy duty cast iron element(s)
- Solid elements deliver heat evenly to pot/pan
 High-tech thermostat offers sensitive variable heat control to keep food simmering or boiling
- Signal light glows only during heat cycle
- Compact size saves precious counter space
- Metal housing with easy to clean surface
- Full one year warranty covering parts and labor
- Non-skid feet 120V NEMA 5-15P plug
- UL Safety & Sanitary / C-UL Freight class 200

• NOTE: Max load capacity of 15 pounds per burner. If using a stockpot or braising pan, no larger than a 1" overhang over element diameter.

Model	Color	Volts	Watts	Amps	Unit Dimensions	Unit Wt.	Ship Wt.	Carton Dimensions	Cube	UPC#
CDR-2CFB	Stainless	120	1800	15	w:131/2", h:41/8", d:223/4"	16 lbs.	20 lbs.	w:161/4", h:91/4", d:273/4"	2.4	654796-64211-3
CDR-2C	Stainless	120	1800	15	w:211/4", h:41/8", d:123/16"	14.4 lbs.	20 lbs.	w:233/8", h:8, d:163/4"	1.74	654796-64206-9
CSR-1CH	Stainless	120	1500	12.5	w:153/8", h:71/2", d:15"	9.5 lbs.	15 lbs.	w:171/2", h:11", d:171/2"	2	654796-61106-5
KR-S2	Stainless	120	1500	12.5	w:111/2", h:3", d:14"	7.2 lbs.	9 lbs.	w:135/8", h:4", d:153/4"	.5	654796-64201-4
KR-1	Black	120	1500	12.5	w:111/2", h:3", d:14"	7.2 lbs.	9 lbs.	w:135/8", h:4", d:153/4"	.5	654796-64000-3

For more information, please contact Cadco, Ltd, 200 International Way, Winsted, CT 06098 Tel. (860)738-2500 • Fax (860) 738-9772 • E-mail: info@cadco-ltd.com • Web site: cadco-ltd.com

