

- ✓ Available in various designs
- ✓ Multi-functional, suitable for any surfaces
- ✓ Ready to install

This light weight, multi-functional surface cleaner is suitable for cleaning any flat surface. You can clean walls and stairs as well as sidewalks and decks. The Universal Line is available in several sizes and styles to fit your needs.



TECHNICAL DATA

Pressure 4000 psi
Temperature 250°F
Inlet 3/8" NPTF

FEATURES

Rotor Arms

Can withstand up to 4000 psi, and are precision welded and balanced.

- 2w2** (2 Arms / 2 Nozzles) Part No. 82.621 (ø 6")
- 2w2** (2 Arms / 2 Nozzles) Part No. 82.623 (ø 10")
- 2w2** (2 Arms / 2 Nozzles) Part No. 82.625 (ø 16")



Proven Innovation

Developed by Mosmatic and in service for years, the toggle swivel has proven itself. The toggle joint feature allows effortless cleaning of walls and angled surfaces. The movement of the joint is adjustable for fatigue free cleaning.



KDYF Toggle Swivel

Part No. 58.908

Swiss Engineering

High rpm stainless steel swivel, features reinforced self lubricated stainless steel ball bearings for improved performance. The dual spring based carbide seal system, guarantees long lasting operation under tough conditions.



DYF Swivel

Part No. 58.000

Stainless Steel Caster

Heavy duty ø 2¼" casters with custom mounting brackets ensure easy maneuvering and longevity.



Stainless Steel Caster

Part No. 80.943



FL-ER 410

FL-EG 410



FL-ER 300

FL-EG 300

FL-EG 200

FL-EB 200

Name	Part No.	ø	Weight	Swivel	Rotor Arm	HP- Nozzles	HP- Gun	Wand	Stainless Steel Caster
FL-EB 200	78.250	8"	4.2 lbs	1x DYF	2x 1/8" NPTF	2x 1503	1x	---	---
FL-EG 200	78.260	8"	5.3 lbs	1x KDYF	2x 1/8" NPTF	2x 1503	1x	1x	---
FL-ER 300	78.262	12"	7.1 lbs	1x KDYF	2x 1/8" NPTF	2x 1503	1x	1x	---
FL-ER 300	78.272	12"	9.5 lbs	1x KDYF	2x 1/8" NPTF	2x 1503	1x	1x	3x ø 2¼"
FL-EG 410	78.264	16"	10.4 lbs	1x KDYF	2x 1/8" NPTF	2x 1503	1x	1x	---
FL-ER 410	78.274	16"	13.0 lbs	1x KDYF	2x 1/8" NPTF	2x 1503	1x	1x	3x ø 2¼"