

- ✓ Easy installation
- ✓ Self rotating and stainless steel
- ✓ Adjustable and non adjustable versions
- ✓ Protection plate available
- ✓ Maintenance free

Clean vent hoods, trash chutes, pipes, totes, manholes and most containers. This self rotating unit is completely maintenance free. The rotating head spins within the protective cage directing the high pressure spray to your surface. The installation is simple and fast.



(81.526)

TYR *adjustable*

The adjustable arms allow different spray angles. Perfect for horizontal ducts and tanks.

warm water		cold water					
TYR-2s	TYR-3s	TRR-2s	TRR-3s	ø	IN	Height	Weight
81.505	81.705	85.505	85.705	3"	1/4" NPTF	2.4"	1.1 lbs
81.506	81.706	85.506	85.706	3"	3/8" NPTF	2.4"	1.1 lbs
81.525	81.725	85.525	85.725	6"	1/4" NPTF	2.8"	2.2 lbs
81.526	81.726	85.526	85.726	6"	3/8" NPTF	2.8"	2.2 lbs
81.555	81.755	85.555	85.755	12"	1/4" NPTF	2.8"	2.8 lbs
81.556	81.756	85.556	85.756	12"	3/8" NPTF	2.8"	2.8 lbs
81.565	81.765	85.565	85.765	16"	1/4" NPTF	2.8"	3.3 lbs
81.566	81.766	85.566	85.766	16"	3/8" NPTF	2.8"	3.3 lbs
81.575	81.775	85.575	85.775	20"	1/4" NPTF	2.8"	3.5 lbs
81.576	81.776	85.576	85.776	20"	3/8" NPTF	2.8"	3.5 lbs
81.585	81.785	85.585	85.785	24"	1/4" NPTF	2.8"	3.9 lbs
81.586	81.786	85.586	85.786	24"	3/8" NPTF	2.8"	3.9 lbs

* Nozzles not included.

Important:
Do not use unprotected!



(81.426)

TYR *fixed*

The non adjustable arms with fixed spray angle is perfect for vertical chutes.

warm water		cold water					
TYR-2f	TYR-3f	TRR-2f	TRR-3f	ø	IN	Height	Weight
81.405	81.605	85.405	85.605	3"	1/4" NPTF	2.4"	1.1 lbs
81.406	81.606	85.406	85.606	3"	3/8" NPTF	2.4"	1.1 lbs
81.425	81.625	85.425	85.625	6"	1/4" NPTF	2.8"	2.2 lbs
81.426	81.626	85.426	85.626	6"	3/8" NPTF	2.8"	2.2 lbs
81.455	81.655	85.455	85.655	12"	1/4" NPTF	2.8"	2.8 lbs
81.456	81.656	85.456	85.656	12"	3/8" NPTF	2.8"	2.8 lbs
81.465	81.665	85.465	85.665	16"	1/4" NPTF	2.8"	3.3 lbs
81.466	81.666	85.466	85.666	16"	3/8" NPTF	2.8"	3.3 lbs
81.475	81.675	85.475	85.675	20"	1/4" NPTF	2.8"	3.5 lbs
81.476	81.676	85.476	85.676	20"	3/8" NPTF	2.8"	3.5 lbs
81.485	81.685	85.485	85.685	24"	1/4" NPTF	2.8"	3.9 lbs
81.486	81.686	85.486	85.686	24"	3/8" NPTF	2.8"	3.9 lbs

* Nozzles not included.

Important:
Do not use unprotected!

TECHNICAL DATA

Pressure	4000 psi	Nozzles	2f/2s for 2x 1/8" Nozzles*
Temperature	TYR 250°F / TRR 90°F	Throughput	3f/3s for 3x 1/8" Nozzles*
Inlet	see chart		ph 3 - 12
Body	stainless steel		
RPM	TYR 2000 rpm / TRR 1000 rpm		