



Keep Your School's Grounds Looking Great with ECHO Outdoor Power Equipment

ECHO is a worldwide leader in the development and manufacture of professional-grade, hand-held outdoor power equipment.



- Your school's grounds make the first impression and ECHO will make it easy for your outdoor crews to keep your campus looking perfectly manicured
- ECHO's full line of outdoor power equipment is easy to start and light weight
- ECHO's industry leading 2-Year Commercial Warranty* provides you with professional-grade and dependable tools

ECHO equipment will help your school's grounds make the grade!

ECHO equipment passes every test with high marks for durability and performance. We have received well over 7,000 peer-reviewed ratings with an average rating of 4.6 out of 5 – that's equivalent to a 92% satisfaction level. *ECHO equipment gets straight A's.*

*2-Year Commercial Warranty includes all engine-driven product categories excluding chain saws. Chain Saws carry a 1-year commercial warranty.



Now is the time to buy ECHO high-performance products for all of your school's lawn equipment needs.

PB-250LN - 44X131

- Outstanding performance, lightweight and low noise
- 25.4 cc handheld blower, gas, professional-grade 2-stroke engine, 391 CFM, 165 MPH



PB-580T - 40JW43

- Combination of economical performance, dependability and comfort
- 58.2 cc backpack blower, gas, professional-grade 2-stroke engine
- 510 CFM, 215 MPH



PB-770T - 44X139

- Industry best combination of air speed and air volume
- 63.3 cc backpack blower, gas, professional-grade 2-stroke engine
- 756 CFM, 234 MPH



CS-490-18 - 52DD57

- Outstanding power and performance
- 50.2 cc, gas, professional-grade 2-stroke engine, reduced effort starter, 16", 18" and 20" bar lengths



CS-590-20 - 20KC05

- Timberwolf™ is the new standard for tough
- 59.8 cc, gas, professional-grade 2-stroke engine, 18" and 20" bar lengths



PPT-280 - 45A335

- Increased power and extra long reach cutting ability
- 28.1 cc, gas, professional-grade 2-stroke engine, 12" bar length and 113" - 158" overall length



HCS-3020 - 52WN53

- Heavy-duty, single-sided performance and 30" blade length
- 21.2 cc professional-grade 2-stroke engine
- 30" RazorEdge™ blades
- Vibration-reduction system



SRM-225 - 44X198

- ECHO's best selling trimmer is also the most fuel efficient
- 21.2 cc professional-grade 2-stroke engine
- 59" straight shaft
- Speed-Feed® 400 head



SRM-266T - 44X203

- Incredible power with 50% more torque
- 25.4 cc professional-grade 2-stroke engine
- 59" straight shaft
- High-capacity Speed-Feed® head



All models are compliant in any state.
For more information contact your Grainger Representative or visit grainger.com.

AVAILABLE THROUGH

GRAINGER

FOR THE ONES WHO GET IT DONE