

BR-EZ316

3/16" Brake Line Replacement Kit

COVERS UP TO
95%
OF REPAIRS



All The Fittings You Need, Best-In-Class Tubing

Everything Needed to Replace Brake Lines Quickly and Easily is Included in These Convenient, All-In-One Kits.

- Pays for itself in as little as one job
- Replace numerous 3/16" brake lines with one kit
- Metric and standard fittings included
- Parts conveniently available, wherever and whenever you need them
- Packaged in durable, portable carrying case
- 1/4" Kit Also Available – PN# BR-EZ14

**110 Pieces, Plus
25' Brake Tubing**

There Is A Difference

Flexible brake tubing makes routing and installation simple



No bending tools required



Brake tubing can be easily bent by hand

ULTRABEND
Brake Line Tubing




1.800.390.3996 • phone: 330.745.3300 • fax: 330.745.3488 • www.surrauto.com

BR-EZ316 KIT CONTENTS

COVERS UP TO
95%
OF REPAIRS

Bold items included in **BR-EZ316 Kit** | *Italic items are available to order.*







ULTRABend® Tubing

IMAGE	PART#	LINE SIZE	DESCRIPTION	QTY
	BR-EZ100	3/16"	3/16" ULTRABend Brake Line	25'
	<i>BR-EZ100-50</i>	<i>3/16"</i>	<i>3/16" ULTRABend Brake Line</i>	<i>50'</i>
	<i>BR-EZ100-100</i>	<i>3/16"</i>	<i>3/16" ULTRABend Brake Line</i>	<i>100'</i>
	<i>BR-EZ200</i>	<i>1/4"</i>	<i>1/4" ULTRABend Brake Line</i>	<i>25'</i>
	<i>BR-EZ200-50</i>	<i>1/4"</i>	<i>1/4" ULTRABend Brake Line</i>	<i>50'</i>
	<i>BR-EZ200-100</i>	<i>1/4"</i>	<i>1/4" ULTRABend Brake Line</i>	<i>100'</i>
	<i>BR-EZ300</i>	<i>5/16"</i>	<i>5/16" ULTRABend Tubing</i>	<i>25'</i>
	<i>BR-EZ400</i>	<i>3/8"</i>	<i>3/8" ULTRABend Tubing</i>	<i>25'</i>

Bubble Flare Nuts

IMAGE	PART#	LINE SIZE	DESCRIPTION	QTY
	BR170	3/16"	3/8" - 24	2
	BR230	3/16"	M10 x 1.0 (Euro, Domestic)	6
	BR235	3/16"	M11 x 1.5	4
	BR240	3/16"	M12 x 1.0	4
	BR245	3/16"	M13 x 1.5	4
	BR250	3/16"	M10 x 1.0 (VW, Audi)	4
	BR255	3/16"	M10 x 1.0 (Ford)	6
	<i>BR2200</i>	<i>1/4"</i>	<i>M12 x 1.0</i>	<i>—</i>
	<i>BR2300</i>	<i>1/4"</i>	<i>M13 x 1.5</i>	<i>—</i>
	<i>BR2500</i>	<i>1/4"</i>	<i>M14 x 1.5 (GM)</i>	<i>—</i>





Adapters

IMAGE	PART#	LINE SIZE	DESCRIPTION	QTY
	BR500	3/16"	3/8" - 24 Inverted Female to M10 x 1.0 Inverted Male	2
	BR505	3/16"	3/8" - 24 Inverted Female to M10 x 1.0 Bubble Male	2
	<i>BR510</i>	<i>3/16"</i>	<i>M10 x 1.0 Bubble Female to M11 x 1.5 Bubble Male</i>	<i>—</i>
	<i>BR550</i>	<i>3/16"</i>	<i>3/8" - 24 Inverted Female to 7/16" - 24 Inverted Male</i>	<i>—</i>
	<i>BR555</i>	<i>3/16"</i>	<i>3/8" - 24 Inverted Female to 1/2" - 20 Inverted Male</i>	<i>—</i>
	<i>BR560</i>	<i>3/16"</i>	<i>3/8" - 24 Inverted Female to 9/16" - 18 Inverted Male</i>	<i>—</i>

Inverted Flare Nuts

IMAGE	PART#	LINE SIZE	DESCRIPTION	QTY
	BR105	3/16"	3/8" - 24	10
	BR135	3/16"	3/8" - 24 Long	10
	BR145	3/16"	7/16" - 24	10
	BR150	3/16"	1/2" - 20	6
	BR155	3/16"	9/16" - 18	6
	BR157	3/16"	3/8" - 24 (7/16" Wrench)	10
	BR205	3/16"	M10 x 1.0 Gold	4
	BR210	3/16"	M10 x 1.0 Blue	6
	BR270	3/16"	M10 x 1.0 Long	6
	<i>BR1150</i>	<i>1/4"</i>	<i>7/16" - 24</i>	<i>—</i>
	<i>BR1200</i>	<i>1/4"</i>	<i>7/16" - 24 (9/16" Wrench)</i>	<i>—</i>
	<i>BR1400</i>	<i>1/4"</i>	<i>7/16" - 24 Long</i>	<i>—</i>
	<i>BR1600</i>	<i>1/4"</i>	<i>9/16" - 18</i>	<i>—</i>
	<i>BR1650</i>	<i>1/4"</i>	<i>1/2" - 20</i>	<i>—</i>

Unions

IMAGE	PART#	LINE SIZE	DESCRIPTION	QTY
	BR405	3/16"	3/8" - 24 Inverted Flare	4
	BR435	3/16"	M10 x 1.0 Inverted Flare	2
	BR450	3/16"	M10 x 1.0 Bubble Flare	2
	<i>BR4100</i>	<i>1/4"</i>	<i>7/16" - 24 Inverted Flare</i>	<i>—</i>

1.800.390.3996 • phone: 330.745.3300 • fax: 330.745.3488 • www.surrauto.com