

BR-EZ14

1/4" Brake Line Replacement Kit

COVERS UP TO
95%
OF REPAIRS



All The Fittings You Need, Best-In-Class Tubing

Everything Needed to Replace Brake Lines Quickly and Easily is Included in These Convenient, All-In-One Kits.

- Pays for itself in as little as one job
- Replace numerous 1/4" brake lines with one kit
- Metric and standard fittings included
- Parts conveniently available, wherever and whenever you need them
- Packaged in durable, portable carrying case
- 3/16" Kit Also Available – PN# BR-EZ316

**40 Pieces, Plus
25' Brake Tubing**

There Is A Difference

Flexible brake tubing makes routing and installation simple.



No bending tools required



Brake tubing can be easily bent by hand

ULTRABEND
Brake Line Tubing




BR-EZ14 KIT CONTENTS

COVERS UP TO
95%
OF REPAIRS

Bold items included in **BR-EZ14 Kit** | *Italic items are available to order.*







ULTRABend® Tubing

IMAGE	PART#	LINE SIZE	DESCRIPTION	QTY
	BR-EZ100	3/16"	3/16" ULTRABend Brake Line	25'
	BR-EZ100-50	3/16"	3/16" ULTRABend Brake Line	50'
	BR-EZ100-100	3/16"	3/16" ULTRABend Brake Line	100'
	BR-EZ200	1/4"	1/4" ULTRABend Brake Line	25'
	BR-EZ200-50	1/4"	1/4" ULTRABend Brake Line	50'
	BR-EZ200-100	1/4"	1/4" ULTRABend Brake Line	100'
	BR-EZ300	5/16"	5/16" ULTRABend Tubing	25'
	BR-EZ400	3/8"	3/8" ULTRABend Tubing	25'

Bubble Flare Nuts

IMAGE	PART#	LINE SIZE	DESCRIPTION	QTY
	BR170	3/16"	3/8" - 24	—
	BR230	3/16"	M10 x 1.0 (Euro, Domestic)	—
	BR235	3/16"	M11 x 1.5	—
	BR240	3/16"	M12 x 1.0	—
	BR245	3/16"	M13 x 1.5	—
	BR250	3/16"	M10 x 1.0 (VW, Audi)	—
	BR255	3/16"	M10 x 1.0 (Ford)	—
	BR2200	1/4"	M12 x 1.0	6
	BR2300	1/4"	M13 x 1.5	—
	BR2500	1/4"	M14 x 1.5 (GM)	—





Adapters

IMAGE	PART#	LINE SIZE	DESCRIPTION	QTY
	BR500	3/16"	3/8" - 24 Inverted Female to M10 x 1.0 Inverted Male	—
	BR505	3/16"	3/8" - 24 Inverted Female to M10 x 1.0 Bubble Male	—
	BR510	3/16"	M10 x 1.0 Bubble Female to M11 x 1.5 Bubble Male	—
	BR550	3/16"	3/8" - 24 Inverted Female to 7/16" - 24 Inverted Male	—
	BR555	3/16"	3/8" - 24 Inverted Female to 1/2" - 20 Inverted Male	—
	BR560	3/16"	3/8" - 24 Inverted Female to 9/16" - 18 Inverted Male	—

Inverted Flare Nuts

IMAGE	PART#	LINE SIZE	DESCRIPTION	QTY
	BR105	3/16"	3/8" - 24	—
	BR135	3/16"	3/8" - 24 Long	—
	BR145	3/16"	7/16" - 24	—
	BR150	3/16"	1/2" - 20	—
	BR155	3/16"	9/16" - 18	—
	BR157	3/16"	3/8" - 24 (7/16" Wrench)	—
	BR205	3/16"	M10 x 1.0 Gold	—
	BR210	3/16"	M10 x 1.0 Blue	—
	BR270	3/16"	M10 x 1.0 Long	—
	BR1150	1/4"	7/16" - 24	6
	BR1200	1/4"	7/16" - 24 (9/16" Wrench)	6
	BR1400	1/4"	7/16" - 24 Long	6
	BR1600	1/4"	9/16" - 18	6
	BR1650	1/4"	1/2" - 20	6

Unions

IMAGE	PART#	LINE SIZE	DESCRIPTION	QTY
	BR405	3/16"	3/8" - 24 Inverted Flare	—
	BR435	3/16"	M10 x 1.0 Inverted Flare	—
	BR450	3/16"	M10 x 1.0 Bubble Flare	—
	BR4100	1/4"	7/16" - 24 Inverted Flare	4

1.800.390.3996 • phone: 330.745.3300 • fax: 330.745.3488 • www.surrauto.com

S.U.R.&R. AUTO PARTS INC. • 1969 S. MAIN ST. • AKRON, OH 44301