MOEN[®] COMMERCIAL

Specifications

FAUCET DESCRIPTION

- Chrome plated brass construction
- Metering faucet designed to deliver either tempered or ambient water.
- Vandal resistant
- Optional 4" deck plate available, purchased separately, 99551 **OPERATION**
- ADA compliant lever style handle
- Cycle time easily adjusted from 5 to 60 seconds, independent . from water pressure
- Operates with water supply line pressures of 20 to 125psi
- Factory preset to automatically shut off after 10 seconds •
- 1/2" IPS supply shank

FLOW

0.5gpm max (1.9 L/min) vandal-resistant multi-stream laminar . flow limits water discharge to a maximum of 0.25gpc (0.95 L/cycle) @ 30 seconds or 0.20qpc (0.76 L/cycle) @ 24 seconds

CARTRIDGE

- 52100 brass shell cartridge cartridge design
- Self contained metering mechanism which is separate from the potable water supply

STANDARDS

- Third party certified to ASME A112.18.1/CSA B125.1, and all applicable specifications referenced therein
- Contains no more than 0.25% weighed average lead content
- ADA (for lever handle
- CalGreen compliant

WARRANTY

Warranted for 5 years against material or manufacturing defects



Single-Handle ADA Metering **Lavatory Faucet**

Model: 8894 (Chrome)

NOTE: DESIGNED TO BE INSTALLED THROUGH 1 HOLE 7/8" MIN. DIA.



CRITICAL DIMENSIONS

(DO NOT SCALE)