



## fitted with

work equipment  
connected load  
power consumption  
light distribution  
beam angle  
light color  
color rendering index  
(CRI) glare-free  
system of protection  
class of protection  
technology  
usage  
luminaire body  
lamp cover  
tubular sections  
balance of articulation  
joints weight (net)  
mains lead  
optional mounting  
special features

## LED

without  
12-28V AC and 12-40V DC  
approx. 8.5 W  
direct, narrow-angled beam  
10°  
neutral white, approx. 5000 K  
> 80  
screen  
IP 20 (67)  
III  
switchable, continuously dimmable  
push button  
aluminium, anodized, black  
glass screen  
flexible metal tube, black  
friction  
approx. 1.8 kg (4 lbs)  
approx. 3,2 m (10.5 ft); with free stranded wires  
table clamp (accessory), wall bracket (accessory)  
spot with 10° angle of radiation

## illuminance

distance: 50 cm

**Em:** 3255 lx  
**E<sub>max</sub>:** 5600 lx  
**E<sub>min</sub>:** 1138 lx

