## **Beltrac® 3000 Series**

*Product innovation engineered for the real world.*<sup>™</sup>



### Premium Post Design

- One-piece, continuous construction.
- Belt mechanism is completely concealed within post.
- Belt mechanism is easily field replaced.
- Post can receive all major manufacturer's belts.

### 4-Way Dovetail Connection

- Standard 4-way connection allows post to deliver one belt while simultaneously receiving three belts or accessories.
- Belt ends connect to all major manufacturers' posts.

### Superior Base Design

- Weighted steel base for superior stability.
- Factory applied, slotted rubberized base protects flooring and promotes air flow, allowing wet floors to dry quickly.
- Optional galvanized base for outdoor use.

### Slow Retracting Belt

• Unique, centrifugal belt-braking system ensures a slow and safe retraction.

### Beltloc<sup>™</sup> – Automatic Belt Locking Option

- Optional metal lock prevents accidental release of belts.
- Locks post-top signs and accessories in place.

### NeXtrac<sup>®</sup> Ready

- Easily add accessories to create flexible, in-line NeXtrac<sup>®</sup> merchandising systems.
- Simple, one-step grip connectors easily attach into "dovetail" grooves.

#### Warranty

• 5 years on posts. 3 years on mechanism.




© 2011 Lavi Industries All Rights Reserved.

# **Beltrac® 3000 Series**

Product innovation engineered for the real world.<sup>™</sup>

		3100	3000DL	3100L	3548	3048, 3005, 3006
	BELTRAC <sup>®</sup> 3000	BELTRAC <sup>®</sup> 3000-13	BELTRAC <sup>®</sup> 3000	BELTRAC <sup>®</sup> 3000-13	BELTRAC <sup>®</sup> 3000	BELTRAC <sup>®</sup> 3000
	40 inches	40 inches	Double Belt 40 inches	Double Belt 40 inches	Mid-Belt Tall Posts 48", 66", 72"	No Belt Tall Posts 48", 66", 72"
Weight	28 lbs.	30 lbs.	28 lbs.	30 lbs.	Varies by height	Varies by height
Finish	Anodized or Lido-Tone <sup>®</sup>	Anodized Satin or Lido-Tone <sup>®</sup>	Anodized or Lido-Tone <sup>®</sup>	Anodized Satin or Lido-Tone <sup>®</sup>	Anodized or Lido-Tone <sup>®</sup> (WB, SA, GD on 48")	Anodized or Lido-Tone <sup>®</sup> (WB, SA, GD on 48")
Post Diameter	2 ¾ inches	3 1/4 inches	2 ¾ inches	3 ¼ inches	2 ¾ inches	2 ¾ inches
Post Construction	Extruded Aluminum	Extruded Aluminum	Extruded Aluminum	Extruded Aluminum	Extruded Aluminum	Extruded Aluminum
Base Connection	Rubber Wedge Insert	Steel Wedge Insert	Rubber Wedge Insert	Steel Wedge Insert	Rubber Wedge Insert	Aluminum Wedge Insert
Base Diameter	14 inches	14 inches	14 inches	14 inches	14" sloped or 20" WB tri-base	14" sloped or 20" WB tri-base
Base Cover	Metal or Plastic	Metal or Plastic	Metal or Plastic	Metal or Plastic	Metal or Plastic No cover on Tri-base	Metal or Plastic No cover on Tri-base
Rubberized Base	Standard	Standard	Standard	Standard	Standard	Standard
Belt Color	All	All	All	All	All	N/A
Belt Length	7 feet	13 feet	7 feet	13 feet	7 feet	N/A
Slow Retracting Belt	Standard	Standard	Standard	Standard	Standard	N/A
Beltloc™	Additional	Additional	Additional	Additional	Additional	N/A
4-Way Connection	Standard	Standard	Standard	Standard	Standard	Optional
Signage Ready	Yes	Yes	Yes	Yes	Yes	Yes
NeXtrac <sup>®</sup> Ready	Yes	Yes	Yes	Yes	Yes	Yes
Outdoor Usage	Add-on, Please call	Add-on, Please call	Add-on, Please call	Add-on, Please call	Add-on, Please call	Add-on, Please call





27810 Avenue Hopkins | Valencia, CA 91355 877.ASK.LAVI | 877.275.5284 | 661.257.7800 sales@lavi.com | www.lavi.com