

MECHANICAL

Auto OFF Springwound In-Wall Timer

A500 Series



SPECIFICATIONS

- Input Voltage: 125/250/277VAC, 50/60Hz
- Terminal Range: #12AWG.
- Operating Temperature: 32 °F to +122 °F (0 °C to +50 °C).

APPLICATIONS

- Whole house fans, indoor/outdoor lighting.
- Bathroom fans and lights, self storage.


FEATURES

- **Variable Timing:** Twist knob for time ON setting. Time ON lengths from 15 minutes to 12 hour vary by model.
- **Hold Feature:** Some models have position for constant ON.
- **Easy-Set:** No adjustments. Just wire and go!
- **Easy Wiring:** No neutral required. Great for retrofit! Use as single or in multi-gang box with no de-rating.
- **Switch Type:** SPDT "2 in 1" contacts wire as SPST also. Can wire normally on and countdown while off.
- **Color:** Ivory, Light Almond, White.
- **Wall Plate:** Fits standard or decorator style wall plates, see below (not included).
- **Caution:** This timer is not to be used in precision timing applications where inaccurate timing could have dangerous consequences (i.e. sun lamp, sauna, etc.).

USE FOR SPST



USE FOR SPDT



CAT. NO.	UPC CODE	HOLD FEATURE	COLOR
15 Minutes Maximum			
A515MH	15020	With Hold	Ivory
A515MHW	15120		White
A515M	15013	No Hold	Ivory
A515MW	15113		White
A515MA	15127		Light Almond
30 Minutes Maximum			
A530MH	15021	With Hold	Ivory
A530MHW	15121		White
A530M	15014	No Hold	Ivory
A530MW	15114		White
A530MA	15128		Light Almond
60 Minutes Maximum			
A560MH	15022	With Hold	Ivory
A560MHW	15122		White
A560M	15015	No Hold	Ivory
A560MW	15115		White
2 Hours Maximum			
A502HHW	15123	With Hold	White
A502H	15016		Ivory
A502HW	15116	No Hold	White
6 Hours Maximum			
A506HHW	15125	With Hold	White
A506H	15018		Ivory
A506HW	15118	No Hold	White
12 Hours Maximum			
A512HH	15026	With Hold	Ivory
A512HHW	15126		White
A512H	15019	No Hold	Ivory
A512HW	15119		White

TYPE	VOLTAGE (VAC)	RATINGS
Resistive	125	20A
	250	10A
	277	10A
Inductive	125	20A
	250	10A
	277	10A
Tungsten	125	7A
Motor	125	1HP
	250	2HP