

# Maxstar® 161 STL

## Genuine Miller® Accessories



### X-CASE™ 301429

Sturdy case provides ultimate protection for transport and storage. Also features convenient top carrying handle and side recessed hand grips. Store the Maxstar 161, accessories and gear in this generous case to be ready to go at any time. Dimensions (H x W x D): 13 x 10.5 x 30.625 in. (330 x 267 x 778 mm).



Female Receptacle

### Full KVA Adapter Cord 300517

NEMA 14-50P to NEMA 6-50R. Adapts engine drive 120/240 V plug to Maxstar 240 V plug.

## Remote Controls and Switches



### RCCS-6M (6-pin plug)

**195184** 13.25 ft. (4 m) cord

**195503** 26.5 ft. (8 m) cord

North/south rotary-motion fingertip current/contacter control attaches to TIG torch using two hook-and-loop fasteners. Great for applications that require a finer amperage control. Includes cord and plug.



### RFCS-6M (6-pin plug)

**195183**

13.25 ft. (4 m) cord

**195504**

20 ft. (6 m) cord

Foot pedal current/contacter control. Includes cord and plug.



### RMS-6M (6-pin plug)

**195269**

Momentary-contact switch for contactor control. Rubber-covered pushbutton dome switch ideal for repetitive on-off applications. Includes 26.5 ft. (8 m) cord and plug.

## TIG Torches

### Weldcraft™ Air-Cooled Torches

**WP-17-12-R** A-150 (WP-17)

12.5 ft. (3.8 m) TIG torch with gas thru connector.

**WP-17-25-R** A-150 (WP-17)

25 ft. (7.6 m) TIG torch with gas thru connector.



### Air-Cooled TIG Torch Connector 195234

25 mm (small) Dinse-style gas thru for one-piece air-cooled torch.

## Ordering Information

Power Source and Options	Stock No.	Description	Qty.	Price
Maxstar® 161 STL Standard Package	907710	Maxstar 161 STL with electrode holder, work clamp, and 120-volt and 240-volt power cords		
Maxstar® 161 STL TIG/Stick Package	907710001	Includes 907710 <i>plus</i> X-CASE™, A-150 TIG torch, gas regulator with hose, and AK2C accessory kit		
	907710002	Includes 907710001 <i>plus</i> remote fingertip control		
Maxstar® 161 STH Standard Package	907711	Maxstar 161 STH with electrode holder, work clamp, and 120-volt and 240-volt power cords		
Maxstar® 161 STH TIG/Stick Package with Remote Fingertip Control	907711001	Includes 907711 <i>plus</i> X-CASE™, A-150 TIG torch, gas regulator with hose, AK2C accessory kit, and remote fingertip control		
<b>Accessories</b>				
X-CASE™ (only)	301429	Carrying case for Maxstar 161		
Full KVA Adapter Cord	300517	Adapts engine drive 120/240 V plug to Maxstar 240 V plug		
RCCS-6M	195184	13.25 ft. (4 m) remote fingertip control		
	195503	26.5 ft. (8 m), remote fingertip control		
RMS-6M	195269	26.5 ft. (8 m) remote on/off control		
RFCS-6M	195183	13.25 ft. (4 m) remote foot control		
	195504	20 ft. (6 m) remote foot control		
Weldcraft™ A-150 (WP-17) TIG Torch		See above		
Air-Cooled TIG Torch Connector	195234	Connects the A-125, A-150 and A-80 Weldcraft torches to 25 mm gas thru Dinse-style connector		

Date:

Total Quoted Price:

Distributed by:

