



BRUTE[®]



STEP RIGHT UP 

TO GET THINGS DONE FASTER



SINCE 1968, BRUTE CONTAINERS have been trusted by professionals for their iconic durability and reliability. The same durability and reliability that have made BRUTE containers the industry's workhorse have also been built into our newest innovation, the BRUTE Step-On Rollout.

The BRUTE Rollout has a step-on mechanism that lifts the lid, allowing for hands-free operation that makes your job easier, every day. BRUTE Rollouts are available in a variety of sizes, styles, and colors to ensure you'll find the optimal solution for any facility need.



HANDS-FREE LID OPERATION

DESIGNED TO HELP PROMOTE PRODUCTIVITY With just a step, the pedal lifts the lid, eliminating the need to keep one hand free to hold the lid open.



EASY TO MOVE



DEPENDABLE SWIVEL CASTERS

Swivel casters at the front of the container distribute weight evenly and allow for more controlled use.



ERGONOMIC REAR HANDLE

Designed for comfortable push or pull operation.



SECURE LID POSITIONING

Rollout lids open fully and stay in place to prevent swinging during transport.



IMPROVED MANEUVERABILITY. The newest addition to the BRUTE family of products is designed with features that help make moving facility waste easier.

FIT FOR FACILITY USE



COMPLIANT WITH AUTO-LIFTERS

Meets ANSI Z245.60 (Types B and G) for compatibility with auto-lifters.



EASY TO CLEAN

Smooth contours and seamless construction help make cleaning easier.



ROBUST WHEELS

Heavy-duty wheels with high-performance treads are optimized for use indoors and outdoors.

DESIGNED SPECIFICALLY FOR FACILITY USE. The BRUTE Rollout can be used throughout commercial environments to allow for easier collection and management of facility waste.



ICONIC DURABILITY



COMMERCIAL-GRADE CONSTRUCTION

High-quality materials plus a UV inhibitor enables use both indoors and outdoors.



TOUGH RIM AND LID STRUCTURE

Reinforced rim for superior structural integrity and robust lid designed for added strength.



EXTREME TEMPERATURES

Designed to maintain performance at freezing temperatures as low as 0° F.



BUILT UPON THE DURABILITY LEGACY OF BRUTE.

The BRUTE Rollout is constructed with high-quality commercial-grade materials to withstand extreme temperatures and perform reliably in the most challenging environments.

BRUTE STEP-ON ROLLOUT WITH CASTERS

	DESCRIPTION	ITEM #	COLOR	PRODUCT WEIGHT (LB)	L (IN)	W (IN)	H (IN)
32 GALLON	BRUTE 32G STEP-ON ROLLOUT WITH CASTERS	1971950	GRAY	22.20	28.56"	20.62"	37.16"
	BRUTE 32G STEP-ON ROLLOUT WITH CASTERS	1971952	BLUE	22.20	28.56"	20.62"	37.16"
50 GALLON	BRUTE 50G STEP-ON ROLLOUT WITH CASTERS	1971962	GRAY	30.00	30.08"	24.00"	39.58"
	BRUTE 50G STEP-ON ROLLOUT WITH CASTERS	1971964	BLUE	30.00	30.08"	24.00"	39.58"
65 GALLON	BRUTE 65G STEP-ON ROLLOUT WITH CASTERS	1971974	GRAY	37.00	32.33"	25.33"	44.74"
	BRUTE 65G STEP-ON ROLLOUT WITH CASTERS	1971976	BLUE	37.00	32.33"	25.33"	44.74"
95 GALLON	BRUTE 95G STEP-ON ROLLOUT WITH CASTERS	1971997	GRAY	46.00	37.15"	28.60"	46.02"
	BRUTE 95G STEP-ON ROLLOUT WITH CASTERS	1971999	BLUE	46.00	37.15"	28.60"	46.02"

COLORS AVAILABLE:  



BRUTE STEP-ON ROLLOUT

	DESCRIPTION	ITEM #	COLOR	PRODUCT WEIGHT (LB)	L (IN)	W (IN)	H (IN)
32 GALLON	BRUTE 32G STEP-ON ROLLOUT	1971944	GRAY	19.20	28.56"	20.62"	37.16"
	BRUTE 32G STEP-ON ROLLOUT	1971946	BLUE	19.20	28.56"	20.62"	37.16"
50 GALLON	BRUTE 50G STEP-ON ROLLOUT	1971956	GRAY	27.00	30.08"	24.00"	39.58"
	BRUTE 50G STEP-ON ROLLOUT	1971958	BLUE	27.00	30.08"	24.00"	39.58"
65 GALLON	BRUTE 65G STEP-ON ROLLOUT	1971968	GRAY	35.50	32.33"	25.33"	44.74"
	BRUTE 65G STEP-ON ROLLOUT	1971970	BLUE	35.50	32.33"	25.33"	44.74"
95 GALLON	BRUTE 95G STEP-ON ROLLOUT	1971991	GRAY	40.00	37.15"	28.60"	46.02"
	BRUTE 95G STEP-ON ROLLOUT	1971993	BLUE	40.00	37.15"	28.60"	46.02"

COLORS AVAILABLE:  



BRUTE ROLLOUT WITH CASTERS

	DESCRIPTION	ITEM #	COLOR	PRODUCT WEIGHT (LB)	L (IN)	W (IN)	H (IN)
32 GALLON	BRUTE 32G ROLLOUT WITH CASTERS	1971947	GRAY	20.70	28.56"	20.62"	37.16"
	BRUTE 32G ROLLOUT WITH CASTERS	1971949	BLUE	20.70	28.56"	20.62"	37.16"
50 GALLON	BRUTE 50G ROLLOUT WITH CASTERS	1971959	GRAY	29.00	30.08"	24.00"	39.58"
	BRUTE 50G ROLLOUT WITH CASTERS	1971961	BLUE	29.00	30.08"	24.00"	39.58"
65 GALLON	BRUTE 65G ROLLOUT WITH CASTERS	1971971	GRAY	36.00	32.33"	25.33"	44.74"
	BRUTE 65G ROLLOUT WITH CASTERS	1971973	BLUE	36.00	32.33"	25.33"	44.74"
95 GALLON	BRUTE 95G ROLLOUT WITH CASTERS	1971994	GRAY	44.00	37.15"	28.60"	46.02"
	BRUTE 95G ROLLOUT WITH CASTERS	1971996	BLUE	44.00	37.15"	28.60"	46.02"

BRUTE MEDICAL WASTE ROLLOUT WITH CASTERS

Locking lids help keep regulated medical waste secure.

	DESCRIPTION	ITEM #	COLOR	PRODUCT WEIGHT (LB)	L (IN)	W (IN)	H (IN)
65 GALLON	BRUTE 65G MEDICAL WASTE ROLLOUT WITH CASTERS	1971977	RED	36.00	32.33"	25.33"	44.74"
95 GALLON	BRUTE 95G MEDICAL WASTE ROLLOUT WITH CASTERS	1972000	RED	44.00	37.15"	28.60"	46.02"

COLORS AVAILABLE:  



COLORS AVAILABLE: 



BRUTE STANDARD ROLLOUT

	DESCRIPTION	ITEM #	COLOR	PRODUCT WEIGHT (LB)	L (IN)	W (IN)	H (IN)
32 GALLON	BRUTE 32G STANDARD ROLLOUT	1971941	GRAY	17.00	28.56"	20.62"	37.16"
	BRUTE 32G STANDARD ROLLOUT	1971943	BLUE	17.00	28.56"	20.62"	37.16"
50 GALLON	BRUTE 50G STANDARD ROLLOUT	FG9W2700GRAY	GRAY	25.00	30.08"	24.00"	39.58"
	BRUTE 50G STANDARD ROLLOUT	FG9W2700BLUE	BLUE	25.00	30.08"	24.00"	39.58"
65 GALLON	BRUTE 65G STANDARD ROLLOUT	FG9W2100GRAY	GRAY	33.50	32.33"	25.33"	44.74"
	BRUTE 65G STANDARD ROLLOUT	FG9W2173BLUE	BLUE	33.50	32.33"	25.33"	44.74"
95 GALLON	BRUTE 95G STANDARD ROLLOUT	FG9W2200GRAY	GRAY	38.50	37.15"	28.60"	46.02"
	BRUTE 95G STANDARD ROLLOUT	FG9W2273BLUE	BLUE	38.50	37.15"	28.60"	46.02"

COLORS AVAILABLE:  





RCP1132

©2016 Rubbermaid Commercial Products LLC
8900 Northpointe Executive Park Drive, Huntersville, NC 28078

To see our complete range of refuse solutions visit our online catalog at rubbermaidcommercial.com

