









AVAILABLE THROUGH

GRAINGER[®]

FOR THE ONES WHO GET IT DONE

GRAINGER.COM[®] | 1.800.GRAINGER

LABELWORKS PX

								
Grainger Item #	490R17 490R18	53RK09	444F43	49AX64	45VZ82	60YR02	60YR54	
PX-Printer	LW-PX300	LW-PX700PCD	LW-PX750	LW-PX800	LW-PX900PCD	LW-Z5000PX	LW-Z5010PX	
Warranty	LIFETIME	LIFETIME	LIFETIME	LIFETIME	LIFETIME	LIFETIME	LIFETIME	
Max Tape Width	3/4" (18 mm)	1" (24 mm)	1" (24 mm)	1.5" (36 mm)	1.5" (36 mm)	2" (50 mm)	2" (50 mm)	
Resolution	180 dpi	180 dpi	180 dpi	360 dpi	360 dpi	300 dpi	300 dpi	
Cutter	Manual	Automatic	Automatic	Automatic	Automatic	Automatic	Automatic	
Half-Cut	No	Yes	Yes	Yes	Yes	Yes	Yes	
(L) Margin (R) Margin	10mm 10mm	4+1mm* 1mm	4+1mm* 1mm	11+1mm* 1mm	4+1mm* 1mm	4+1mm* 1mm	4+1mm* 1mm	
Import Graphics	No	From PC	From PC	From PC or Mobile	From PC	From PC or Mobile	From PC or Mobile	
Import Spreadsheet	No	From PC	From PC	From PC	From PC	From PC	From PC	
PC Connect	No	Yes	Yes	Yes	Yes	Yes	Yes	
Wireless	No	No	No	Yes	No	Yes	Yes	
Bluetooth™	No	No	No	No	No	No	No	
AC Power	Yes	Yes	Yes	Yes	Yes	Yes	Yes	
Batteries	6AA (not included)	6AA (not incl.) Li-ion (included)	6AA (not included)	N/A	6AA (not incl.) Li-ion (included)	No	Li-ion	
Max Print Speed	6mm/sec	30mm/sec	30mm/sec	35mm/sec	35mm/sec	50mm/sec	50mm/sec	
Mobile Apps**	No	No	No	Yes	No	Yes	Yes	
PeelGuard	No	No	Yes	Yes	No	No	No	
Bulk Printing	No	No	No	No	No	Yes	Yes	
Rewinder	No	No	No	No	No	Yes	Yes	

*The first number before the (+) is the lead margin on the first print or single printed label. The (+) can be either a full or half-cut. When printing batches of labels, the margin can be reduced to 1mm (only available on models LW-PX400, LW-PX700, LW-PX750, LW-PX800, LW-PX900, LW-Z5000PX and LW-Z5010PX).

**Mobile Apps, Epson iLabel and Epson Datacom available for both Android and iOS devices.