

Dial Test Indicators 3808, 3809, 3908 & 3909 Series

These dial test indicators are offered with choices of dial size, range and include accessories.

All 3808 and 3809 models have 1-1/4" (32mm) dial faces while 3908 and 3909 models offer a larger 1-9/16" (40mm) dial face.

Each inch reading and metric reading 3808, 3809, 3908 and 3909 is offered with a choice of two Graduation/Range/Reading configurations.

Features & Specifications

- Three dovetail positioning mounts work with most existing test indicator accessories
- Precision gear-driven design with smooth, jeweled movement
- Contact point reverses automatically, always maintaining clockwise hand rotation
- Frictionally adjustable contacts
- Meets or exceeds ANSI/ASME accuracy specifications
- High contrast, easy-to-read dials with white background for inch and yellow for metric
- Satin chrome finish



3808, 3809, 3908 & 3909 Inch Reading Indicators						
Grad	Range	Dial Reading	Dial Diameter	Description	Cat. No.	EDP
.0001"	.008"	0-4-0	1-1/4"	Indicator, two dovetail clamps, case*	3808A	12331
				Indicator with accessories, case**	3808AC	12303
			1-9/16"	Indicator, two dovetail clamps, case*	3908A	12488
				Indicator with accessories, case**	3908AC	12636
.0005"	.030"	0-15-0	1-1/4"	Indicator, two dovetail clamps, case*	3809A	12333
				Indicator with accessories, case**	3809AC	12305
			1-9/16"	Indicator, two dovetail clamps, case*	3909A	12527
				Indicator with accessories, case**	3909AC	12669

* Indicator, .156" contact point, 3/8" & 5/32" dovetail clamps & case

** Indicator, .078" & .156" contact points, 3/8" & 5/32" dovetail clamps, .156" swivel post holder, tool post holder, contact wrench & case

3808, 3809, 3908 & 3909 Metric Reading Indicators						
Grad	Range	Dial Reading	Dial Diameter	Description	Cat. No.	EDP
0.002mm	0.2mm	0-100-0	32mm	Indicator, two dovetail clamps, case*	3808MA	12332
				Indicator with accessories, case**	3808MAC	12304
			40mm	Indicator, two dovetail clamps, case*	3908MA	12520
				Indicator with accessories, case**	3908MAC	12656
0.01mm	0.8mm	0-40-0	32mm	Indicator, two dovetail clamps, case*	3809MA	12334
				Indicator with accessories, case**	3809MAC	12307
			40mm	Indicator, two dovetail clamps, case*	3909MA	12563
				Indicator with accessories, case**	3909MAC	12673

* Indicator, 4mm contact point, 9.5mm & 4mm dovetail clamps & case

** Indicator, 2mm & 4mm contact points, 9.5mm & 4mm dovetail clamps, 4mm swivel post holder, tool post holder, contact wrench & case



AC & MAC indicators include two contact points, two dovetail clamps, swivel post holder, tool post holder, contact wrench and case



A & MA indicators include two dovetail clamps and case

