

Low Profile LED Wraparound



wraps



FEATURES

- Long-life 50,000 hour LEDs at L80 for reduced maintenance
- Four LED color choices
- 4' Size offers three lumen packages
- 2' Size offers two lumen packages
- Superior color consistency within a 3-step MacAdam ellipse and greater than 80 CRI
- Optional integral emergency battery pack
- Heavy gauge steel housing, die embossed for maximum rigidity
- White steel end plates
- Diffuser features flat bottom and vertical sides
- Hinges from either side
- LED boards and driver accessible for future maintenance or upgrades; modular, replaceable
- DesignLights Consortium® (DLC) qualified; see www.designlights.org
- Surface Mount or Suspended
- For narrow corridor wrap with matching appearance use LRO
- QR code traceability
- Five year warranty (Terms and Conditions apply)

ORDERING INFORMATION

LAW						U	
MODEL	SIZE	COLOR TEMP	LUMEN OUTPUT	DRIVER	VOLTAGE	OPTIONS	
LAW LED Wraparound	2 2'	30 3000K	LW Low Watt	E Fixed Output	U 120V-277V	ELL14 Emergency Battery Pack Installed, 1400 Lumens ^{1,2}	
	4 4'	35 3500K	ML Medium Lumen	ESD Step Dimming		GLR Fast Blow Fuse	
		40 4000K	HL High Lumen	ED 0-10V Dimming		PAF Paint After Fabrication	
		50 5000K	See Product Availability Table below.	ED1 0-10V 1% Dimming		NYC NYC Compliant	
				LUTH Lutron H Series			
				LUT5 Lutron 5 Series			

ACCESSORIES (ORDER SEPARATELY)

- S18** 18" Stem, Canopy
- SS18** 18" Swivel Stem—45° Swivel

¹ For compatibility with Dual-Lite LiteGear® inverters in lieu of installed Battery Pack, contact Hubbell Lighting Representative.

² Only available in 4 ft.

PRODUCT AVAILABILITY

SIZE	LUMEN PACKAGE	NOMINAL LUMENS	NOMINAL WATTS	EFFICACY
2'	LW	2,600	25	105
	ML	4,300	49	88
4'	LW	2,500	23	109
	ML	4,700	48	98
	HL	5,600	55	102

Lumens vary according to color temperatures and other factors. See specific photometric test(s).

