

Protect It! 3-Outlet Surge Protector with Mounting Brackets, 10 ft. Cord, 510 Joules, 2 USB Charging Ports, Black Housing

MODEL NUMBER: TLP310USBS



Mounts safely to your workstation to safeguard your computer, scanner and other electronics against surges, spikes and line noise, as well as charge mobile devices, including smartphones, tablets and MP3 players.

Description

The TLP310USBS Protect It!® 3-Outlet Surge Protector features three NEMA 5-15R outlets and a surge suppression rating of 510 joules to protect your components against surges, spikes and EMI/RFI line noise that can damage sensitive electronics and destroy data. Plus, two USB ports produce 3.1A of combined power to charge your mobile devices, such as smartphones, tablets and MP3 players.

Recommended for home, office, workstations and dorm rooms, the TLP310USBS includes two sets of brackets and hardware for permanent mounting in, on or under your desk or workstation. The 10-foot power cord is long enough to reach distant AC outlets. Tripp Lite will repair or replace any connected equipment damaged by surges, including direct lightning strikes, up to \$20,000 for life (valid in the U.S., Canada and Puerto Rico only).

Features

Powers and Protects Electronic Components

- 3 NEMA 5-15R outlets accept most computers and peripherals
- 510 joules of surge suppression protect against surges, spikes and EMI/RFI line noise
- Recommended for home, office, workstations and dorm rooms

Powers and Charges Mobile Devices

- 2 USB ports (3.1A total) charge smartphones, tablets and other devices

Mounts Safely to a Variety of Locations

Highlights

- Mounts in, on or under most desks, tables and workstations
- 3 NEMA 5-15R outlets and 2 USB charging ports (3.1A total)
- 510 joules of surge suppression
- 10 ft. power cord reaches distant AC outlets

Package Includes

- TLP310USBS Protect It! 3-Outlet Surge Protector
- (4) Mounting Brackets
- (8) 6-32 flat-head machine screws
- (6) M4-16T Truss-head self-tapping screws
- Owner's manual



- Attaches permanently in, on or under most desks, tables and workstations
- Includes 2 sets of mounting brackets and hardware

\$20,000 Ultimate Lifetime Insurance

- Tripp Lite will repair or replace any connected equipment damaged by surges, including direct lightning strikes, up to \$20,000 for life
- Valid in the U.S., Canada and Puerto Rico only

Specifications

| OVERVIEW | |
|--|--------------|
| UPC Code | 037332198471 |
| OUTPUT | |
| Charging Ports / Amps | (2) 3.1A |
| Frequency Compatibility | 60 Hz |
| Output (Watts) | 1800 |
| Output Receptacles | (4) 5-15R |
| Circuit Breaker (amps) | 15 |
| Right-Angle Outlets | No |
| INPUT | |
| Nominal Input Voltage(s) Supported | 120V AC |
| Recommended Electrical Service | 120V |
| Input Cord Length Details | Strip |
| Voltage Compatibility (VAC) | 120 |
| Input Plug Type | NEMA 5-15P |
| Input Cord Length (ft.) | 10 |
| Right-Angle Plug | No |
| Input Cord Length (m) | 3.05 |
| Integrated Cord Clip | No |
| USER INTERFACE, ALERTS & CONTROLS | |
| Diagnostic LED(s) | Yes |
| SURGE / NOISE SUPPRESSION | |
| AC Suppression Joule Rating | 510 |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| | |
|-------------------------------------|--|
| AC Suppression Response Time | < 1ns |
| Protection Modes | Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression |
| Clamping Voltage (RMS) | 1000 |
| UL1449 Let Through Rating | 1000 |
| EMI / RFI Filtering | Yes |
| Immunity | Conforms to IEE 587/ANSI C62.41 |
| Automatic Shut-Off | No |
| DATALINE SURGE SUPPRESSION | |
| Telephone/DSL Protection | No |
| Cable (Coax) Protection | No |
| Network (Ethernet) Protection | No |
| PHYSICAL | |
| Anti-Microbial Protected | No |
| Color | Black |
| Color (AC Line Cord) | Black |
| Housing Color | Black |
| Included Mounting Accessories | Mounting brackets |
| Integrated Keyhole Mounting Slots | No |
| Material of Construction | Plastic |
| Receptacle Color | Black |
| Shipping Dimensions (hwd / cm) | 22.86 x 6.35 x 13.72 |
| Shipping Dimensions (hwd / in.) | 9.00 x 2.50 x 5.40 |
| Shipping Weight (kg) | 0.86 |
| Shipping Weight (lbs.) | 1.90 |
| Unit Dimensions (hwd / cm) | 5.59 x 18.39 x 3.91 |
| Unit Dimensions (hwd / in.) | 2.2 x 7.24 x 1.54 |
| SPECIAL FEATURES | |
| Rotatable Outlets | No |
| CERTIFICATIONS | |
| UL1449 3rd Edition (AC Suppression) | UL1449, UL962A |
| Approvals | RoHS |
| WARRANTY | |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| | |
|--|---|
| Product Warranty Period (Worldwide) | Lifetime limited warranty |
| Connected Equipment Insurance (U.S., Canada & Puerto Rico) | \$20,000 Ultimate Lifetime Insurance |

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>