

# 8066 CamView IP Pro-8W HD CCTV Tester

**Portability, user-friendly design and many other functions make this IP tester an essential tool for all installers and technicians**

## Features:

- Designed for the maintenance and installation of IP cameras, analog cameras, TVI, CVI, AHD cameras, as well as testing 4K H.264 /4K H.265 cameras by mainstream
- Ideal tester for security camera installers and technicians
- Has PoE (24W) and DC power output (12V/3A)
- Includes Hikvision and Dahua apps plus over 30 additional protocols
- Network test including Ping/IP Scan/Port Flash/Link Monitor
- Includes Li-ion battery, AC adapter/charger, BNC/BNC cable, RS485 cable, audio cable, 12V camera power cable, wrist strap, and carrying case
- One year warranty



## Specifications

IPC Protocol	ONVIF, RTSP, RTP
Network Test	10/100/100M detect; IP address scan, ping, packet test, DHCP server; trace route; link monitor
Rapid IP Discovery	Discover the IP address in the connected device's network segment
WiFi	Display upload/download connection speeds; create a Wifi hotspot
IP Camera Test	Display image from the 4K H.265 camera by mainstream
Data Monitor	Capture and analyze the command data from controlling device; can also send hexadecimal
Video Test	NTSC/PAL/HD-CVI 3.0/AHD 3.0/HD-TVI 3.0
Audio Test	1 channel audio signal input
PTZ Control Test	Support RS485; Compatible with more than 30 protocols
Lens Simulation	Simulate different lens display areas: 2.8, 3.6, 4, 6, 8, 12, 16, 25mm
POE Test Power	48V power output; Max power 24W
12V Power Output	12V/3A output interface
Snapshot/Video	Capture and record images and live video with playback
Memory	Internal: 3.2GB; External: optional microSD 32GB max
Display	4" IPS touchscreen, 800 x 480
Power	Lithium-ion battery; 8 hour work time
Dimensions	5 x 3.3 x 1.3" (126 x 83 x 33mm)



*Compact and lightweight wrist strap design keeps your hands free*

## Ordering Information:

8066 CamView IP Pro 8W CCTV Camera Tester

