

70424

Compact Wall/Deck Scrub, 8.86" Hard, Red



Clean around equipment and against walls and comply with HACCP principles with this colour-coded Deck/Wall Scrub. Features angled bristles around the perimeter and a rounded, compact design for improved durability.

Technical Data

Item Number	70424
Visible bristle length	1,65 "
Material	Polyester Polypropylene Stainless Steel (AISI 304)
Complies with (EC) 1935/2004 on food contact materials ¹	Yes
Produced according to EU Regulation 2023/2006/EC of Good Manufacturing Practice	Yes
FDA-compliant raw material (CFR 21)	Yes
Meets the REACH Regulation (EC) No. 1907/2006	Yes
Use of phthalates and bisphenol A	No
Is Halal and Kosher compliant	Yes
Box Quantity	10 Pcs.
Quantity per Pallet (80 x 120 x 200 cm)	800 Pcs.
Quantity Per Layer (Pallet)	80 Pcs.
Length	8,86 "
Width	2,95 "
Height	4,53 "
Net Weight	0,7275 lbs
Tare plastic packaging	0,02 lbs
Tare Cardboard	0,03 lbs
Tare Total	0,04 lbs
Gross Weight	0,7716 lbs
Cubic Feet	0,0686 ft ³
Recommended sterilisation temperature (Autoclave)	249,8 °F
Max. cleaning temperature (Dishwasher)	199,4 °F
Max usage temperature (food contact)	176 °F
Max usage temperature (non food contact)	212 °F
Min. usage temperature	-4 °F
Max. drying temperature	212 °F
Min. pH-value in usage concentration	2 pH
Max. pH-value in Usage Concentration	10,5 pH
GTIN-13 Number	5705022021433
GTIN-14 Number (Box quantity)	15705028021441
Customs Tariff No.	96039099
Country of Origin	Denmark
Box length	14,96 "

Box Width	11,42 "
Box Height	6,89 "

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care units, before use.

1. See Declaration of Compliance for further details on food contact
3. Do not store the product below 32 °Fahrenheit.