











## Wallplates

### Non-metallic Plates

- High-impact polycarbonate thermoplastic is virtually unbreakable
- Smooth satin finish, blends into the wall
- Screws are factory-inserted for fumble-free installation

### Stainless Steel Plates

- Type 302/304
- Non-magnetic
- Ideal for highly corrosive environments

Description	Color	Thermoplastic		Material	Metal Catalog Number
		Standard	Mid-Size		
 1-Gang, 1-Toggle	Black Brown Gray Ivory White	<b>P1BK</b> <b>P1</b> <b>P1GY</b> <b>P1I</b> <b>P1W</b>	<b>PJ1BK</b> <b>PJ1</b> <b>PJ1GY</b> <b>PJ1I</b> <b>PJ1W</b>	Brass Stainless Steel	<b>SB1</b> <b>SS1</b>
 1-Gang, 1-Duplex	Black Brown Gray Ivory White	<b>P8BK</b> <b>P8</b> <b>P8GY</b> <b>P8I</b> <b>P8W</b>	<b>PJ8BK</b> <b>PJ8</b> <b>PJ8GY</b> <b>PJ8I</b> <b>PJ8W</b>	Brass Stainless Steel	<b>SB8</b> <b>SS8</b>
 1-Gang, 1-Decorator	Black Brown Gray Ivory White	<b>P26BK</b> <b>P26</b> <b>P26GY</b> <b>P26I</b> <b>P26W</b>	<b>PJ26BK</b> <b>PJ26</b> <b>PJ26GY</b> <b>PJ26I</b> <b>PJ26W</b>	Brass Stainless Steel	<b>SB26</b> <b>SS26</b>
 2-Gang, 2-Toggle	Black Brown Gray Ivory White	<b>P2BK</b> <b>P2</b> <b>P2GY</b> <b>P2I</b> <b>P2W</b>	<b>PJ2BK</b> <b>PJ2</b> <b>PJ2GY</b> <b>PJ2I</b> <b>PJ2W</b>	Brass Stainless Steel	<b>SB2</b> <b>SS2</b>
 2-Gang, 2-Duplex	Black Brown Gray Ivory White	<b>P82BK</b> <b>P82</b> <b>P82GY</b> <b>P82I</b> <b>P82W</b>	<b>PJ82BK</b> <b>PJ82</b> <b>PJ82GY</b> <b>PJ82I</b> <b>PJ82W</b>	Brass Stainless Steel	<b>SB82</b> <b>SS82</b>
 2-Gang, 2-Decorator	Black Brown Gray Ivory White	<b>P262BK</b> <b>P262</b> <b>P262GY</b> <b>P262I</b> <b>P262W</b>	<b>PJ262BK</b> <b>PJ262</b> <b>PJ262GY</b> <b>PJ262I</b> <b>PJ262W</b>	Brass Stainless Steel	<b>SB262</b> <b>SS262</b>
 2-Gang, 1-Toggle, 1-Duplex	Black Brown Gray Ivory White	– <b>P18</b> <b>P18GY</b> <b>P18I</b> <b>P18W</b>	<b>PJ18BK</b> <b>PJ18</b> <b>PJ18GY</b> <b>PJ18I</b> <b>PJ18W</b>	Brass Stainless Steel	<b>SB18</b> <b>SS18</b>
 2-Gang, 1-Toggle, 1-Decorator	Black Brown Gray Ivory White	<b>P126BK</b> <b>P126</b> <b>P126GY</b> <b>P126I</b> <b>P126W</b>	<b>PJ126BK</b> <b>PJ126</b> <b>PJ126GY</b> <b>PJ126I</b> <b>PJ126W</b>	Brass Stainless Steel	<b>SB126</b> <b>SS126</b>
 1-Gang, 1-Single 1.40" Dia. Hole	Black Brown Gray Ivory White	<b>P7BK</b> <b>P7</b> <b>P7GY</b> <b>P7I</b> <b>P7W</b>	<b>PJ7BK</b> <b>PJ7</b> <b>PJ7GY</b> <b>PJ7I</b> <b>PJ7W</b>	Brass Stainless Steel	<b>SB7</b> <b>SS7</b>
 1-Gang, 1-Blank, Box Mount	Black Brown Gray Ivory White	<b>P13BK</b> <b>P13</b> <b>P13GY</b> <b>P13I</b> <b>P13W</b>	<b>PJ13BK</b> <b>PJ13</b> <b>PJ13GY</b> <b>PJ13I</b> <b>PJ13W</b>	Brass Stainless Steel	<b>SB13</b> <b>SS13</b>