

The ultimate rechargeable lantern.

This 2-in-1 lantern/flashlight combo provides 360° of light to illuminate a large area or a focused beam to light your path. Multiple modes plus SOS for emergency signaling. It accepts the Streamlight SL-B26® protected Li-Ion USB rechargeable battery pack or two CR123A lithium batteries, so you'll always have a beam when you need it.



Multiple modes:

- **White Light (Lantern):**
 - » High for brightest light: 325 lumens; runs 4.5 hours
 - » Medium for bright light and longer run time: 170 lumens; runs 7.75 hours
 - » Low for extended run time when less light is needed: 30 lumens; runs 25 hours
- **Red Light (Lantern):**
 - » High: 1.6 lumens; runs 22 hours
 - » Flash SOS mode for emergency signaling: 1.6 lumens; runs 90 hours
- **Flashlight mode:**
 - » High: 300 lumens; runs 3.5 hours
 - » Low: 40 lumens; runs 25 hours

Tough, polycarbonate thermoplastic construction with elastomer over mold; Unbreakable polycarbonate lenses

IPX7 waterproof to 1m submersion; 2m impact resistance tested

4.35" (11.05 cm); 7.2 oz. (204.12g) SL-B26 battery pack;
6.8 oz. (192.78g) CR123A batteries

Limited Lifetime Warranty
Visit streamlight.com for full warranty information

#44956 - Siege X USB - SL-B26 battery pack, USB cord - Coyote