

Inspect, identify and repair with the super-compact FlipMate. It produces bright white light for everyday use or high CRI light with Streamlight's Color-Rite Technology™ to identify color differences in paint or wires.

Fits comfortably in the palm of your hand, allowing you to illuminate hard-to-get-to spaces, like under the dash. Go hands-free with the flat, magnetic base and stowable hook.



270° rotating light bar aims the beam where you need it

Double-function light bar:
 1.) 90 CRI LEDs - Color-Rite Technology - distinguish between similar colors - for paint matching, checking wires, etc.
 2.) Cool white LEDs for bright, white light
 Each with high and low modes



USB rechargeable
 Lithium ion battery
 recharges in 4.5 hours



Stowable hang hook



Hands-free applications:
 1.) Magnetic base
 2.) Stowable hang hook
 3.) Foot provides stability to stand on end

Operating modes:

- Cool white LEDs for bright, white light:
 - » High: 500 lumens; runs 2.5 hours
 - » Low: 250 lumens; runs 5.75 hours
- 90 CRI LEDs - Streamlight's Color-Rite Technology™ - to better see the color spectrum:
 - » High: 400 lumens; runs 2.5 hours
 - » Low: 200 lumens; runs 6 hours

Durable, anodized aluminum construction; unbreakable polycarbonate lens

IPX4 water resistant; 2m impact resistance tested

Folded length: 4.58" (11.63 cm); Extended length: 7.94" (20.17 cm); 8.7 oz. (247g)

Limited Lifetime Warranty
 Visit streamlight.com for full warranty information

- #61500 - FlipMate - with USB cord - Black
- #61501 - FlipMate - with USB cord - Red
- #61502 - FlipMate - with USB cord - Blue