

## Additional Features



### EZ-Change™ Low Cylinder Rack

- Operators no longer need to lift cylinders. Cylinders now easily roll on and off our EZ-Change™ low cylinder rack.



### Dual Front Handles

- Split handle with rubber grips designed to move machine easily and provide quick accessibility to work lead and TIG torch.
- Handles provide protection for front panel.



### Integrated Storage Compartment and Parameter Chart

- Convenient compartment allows for easy storage of cables, foot controls and power cord adapters in the machine.



### EZ-Access™ Consumable Compartment

- Convenient flip-down compartment contains storage for consumables (sold separately).

## Genuine Miller® Accessories



### Dual EZ-Change™ Low Cylinder Rack with Elevated Gun and Cable Rack 300337

Dual cylinder rack allows operators to easily roll cylinders on and off the rack with no lifting. Gun and cable rack keeps cables off the floor and tangle free.

**Elevated Gun and Cable Rack 300335**  
For use with single cylinder rack. (Included with Dual EZ-Change Low Cylinder Rack.)



### Protective Cover 195142

Features side pocket. (Not for use with Dual Cylinder Rack or Elevated Gun and Cable Rack.)



### TIG Torch Accessory Kit AK-150MFC

Allows welding operators to customize their standard Weldcraft™ A-150 (WP-17) TIG

torch for their specific application. Kit converts into 28 different torch styles while using the existing cable. Features nozzles, collets, collet bodies, torch heads, handle and more.



### Performance TIG Gloves

**263345** X-Sm (Women's)  
**263346** Small (Women's)  
**263347** Medium  
**263348** Large  
**263349** X-Large  
Completely unlined, goat grain leather with triple-padded palm.



### Performance MIG Gloves (Unlined)

**263335** Medium  
**263336** Large  
**263337** X-Large  
Unlined, dual-padded cow grain palm with goat grain fingers and double-layer insulated back.

### TIG Memory Cards

#### Memory Card (Blank) 301080

Used for transferring software updates and expandable features from your computer to the machine.

### Spoolmate™ 100 Consumables



#### Contact Tips (5 per package)

**199730** For .024-inch (0.6 mm) wire.  
**186419** For .030-inch (0.8 mm) wire.  
**186406** For .035-inch (0.9 mm) wire.




#### Nozzle 186405

### Spoolmate™ 150 Consumables



#### Contact Tips (5 per package)

**199387** For .030-inch (0.8 mm) wire.  
**199388** For .035-inch (0.9 mm) wire.



#### Nozzle 050622

## Genuine Miller® Accessories (Continued)

### Remote Controls



#### Wireless Remote Foot Control 300429

For remote current and contactor control. Receiver plugs directly into the 14-pin receptacle of Miller machine. 90-foot (27.4 m) operating range.

14-pin receptacle of Miller machine. 90-foot (27.4 m) operating range.



#### RFCS-14 HD Foot Control 194744

Maximum flexibility is accomplished with a reconfigurable cord that

can exit the front, back or either side of the pedal. Foot pedal provides remote current and contactor control. Includes 20-foot (6 m) cord and 14-pin plug.



#### RCC-14 Remote Contactor and Current Control 151086

East/west rotary-motion fingertip control attaches to TIG torch using two hook-and-loop fasteners. Includes 26.5-foot (8 m) control cord and 14-pin plug.



#### RCCS-14 Remote Contactor and Current Control 043688

North/south rotary-motion fingertip control attaches to TIG torch using two hook-and-loop fasteners. Includes 26.5-foot (8 m) control cord and 14-pin plug.



#### RHC-14 Hand Control 242211020

Miniature hand control for remote current and contactor control. Dimensions: 4 x 4 x

3.25 inches (102 x 102 x 83 mm). Includes 20-foot (6 m) cord and 14-pin plug.

### Educational Materials

To order, please call Miller Literature at 866-931-9732 or visit [MillerWelds.com/resources/tools](http://MillerWelds.com/resources/tools).

#### Gas Tungsten Arc (TIG) Welding Publication 250833

## Ordering Information

Equipment and Options	Stock No.	Description	Qty.	Price
<b>Syncrowave® 210 Runner TIG/MIG Complete</b>	<b>951684</b>	Auto-Line™ 120–240 V, 50/60 Hz, Spoolmate™ 150		
<b>Accessories</b>				
Dual EZ-Change Low Cylinder Rack	<b>300337</b>	Includes Elevated Gun and Cable Rack		
Elevated Gun and Cable Rack	<b>300335</b>	For use with single cylinder rack		
Protective Cover	<b>195142</b>			
Weldcraft™ A-150 (WP-17) TIG Torch	<b>WP-17-12-MF</b> <b>WP-17-25-MF</b>	12.5 ft. (3.8 m) cable (included with Runner package) 25 ft. (7.6 m) cable		
Air-Cooled TIG Torch Connector	<b>194722</b>	Connects the A-125, A-150 and A-80 Weldcraft™ torches to 50 mm gas thru Dinse-style connector		
TIG Torch Accessory Kit	<b>AK-150MFC</b>			
TIG Gloves		See page 3		
<b>TIG Memory Cards</b>				
Memory Card (Blank)	<b>301080</b>			
<b>Spool Gun and Consumables</b>				
Spoolmate™ 100 Spool Gun	<b>300371</b>	Includes 12 ft. (3.7 m) cable and custom carrying case		
Spoolmate™ 150 Spool Gun	<b>301272</b>	Includes 20 ft. (6 m) cable (included with Runner package)		
Adapter Kit	<b>301254</b>	Includes adapters required to connect Spoolmate to Syncrowave 210 (included with Runner package)		
Contact Tips		See page 3		
Nozzles		See page 3		
<b>Remote Controls</b>				
Wireless Remote Foot Control	<b>300429</b>	Foot control with wireless 90 ft. (27.4 m) operating range		
RFCS-14 HD	<b>194744</b>	Heavy-duty foot control (included with Runner package)		
RCC-14	<b>151086</b>	Side-to-side (east/west) fingertip control		
RCCS-14	<b>043688</b>	North/south fingertip control		
RHC-14	<b>242211020</b>	Hand control		
<b>Educational Resources</b>				
Gas Tungsten Arc Welding (TIG) Publication	<b>250833</b>			

Date:

Total Quoted Price:

Distributed by:

