

# DEWALT®

12V<sup>MAX\*</sup>

20V<sup>MAX\*</sup>

**ADJUSTABLE BRIGHTNESS**  
3 Brightness Settings  
Up to 2000 lumens

**TRIPOD MOUNT**  
Standard 5/8" and 1/4"  
Universal Thread Mount

**360 DEGREE HANDLE**  
Rotational Handle is optimized  
for 12V and 20V MAX compact  
batteries



**COLOR TEMPERATURE**  
4000k Natural Daylight Hue

**COMPACT DESIGN**  
2.8 lbs (tool only) for  
Ease of Portability and  
Handheld Use

\* Maximum initial battery voltage (measured without a workload) is 12 and 20 volts. Nominal voltage is 10.8 and 18.

**12V/20V MAX\* CORDLESS TASK LIGHT**

**DCL077B**



› 3 Settings for added control



› Only 2.8 lbs for portability

## SPECIFICATIONS

Height	7.4"
Width	4.8"
Length	9.6"
Weight	2.8 lbs
Lumens	2000 Max Output

### TOOL WARRANTY

<b>3</b> YEAR LIMITED WARRANTY	<b>1</b> YEAR FREE SERVICE	<b>90</b> DAY MONEY BACK GUARANTEE
---	-------------------------------------	---

## RELATED PRODUCTS



**DCB240**  
20V MAX\* COMPACT 4Ah BATTERY



**DCL074**  
TOOL CONNECT 20V MAX\* ALL-PURPOSE  
WORK LIGHT



**DW0737**  
CONSTRUCTION TRIPOD



**DCL079B**  
20V MAX\* CORDLESS  
TRIPOD LIGHT

**www.DEWALT.com 1-800-4-DEWALT**

Copyright ©2020 DEWALT. The following are examples of trademarks for one or more DEWALT power tools, accessories, anchors, and concrete adhesives: the yellow and black color scheme; the "D"-shaped air intake grill; the array of pyramids on the handgrip; the kit box configuration; and the array of lozenge-shaped humps on the surface of the tool.