



Main

Range of product	9080G
Product	Terminal block fusible
Product or component type	Terminal block
Color	Natural
Quantity	Set of 10

Complementary

Voltage Rating	600 V AC/DC
Current Rating	30 A UL 30 A CSA
Wire Size	AWG 18...AWG 10 copper
Mounting Type	35 mm DIN rail 9080GH track
Certifications	CSA file 62144 class 6228 01 CE UL recognized E60616 CCN XCFR2
Protection Type	Fingersafe DIN 57470
Electrical Connection	pressure wire clamp
Material	Nylon block Tin plated copper busbar
Ambient air temperature for operation	-40...105 °C (-40...221 °F)
Electrical Connection Tightening Torque	Clamp terminal zinc plated steel 2.03...2.26 N.m (18...20 lbf.in) : AWG 18...AWG 10 copper)
Height	59.18 mm (2.33 in)
Width	55.63 mm (2.19 in)
Depth	19.05 mm (0.75 in)
Density	16 per foot
Compatible End Barrier	GF6B

Ordering and shipping details

Category	21702 - 9080 G (NOT GCB)
Discount Schedule	CP5
GTIN	00785901155034
Package weight(Lbs)	0.03 kg (0.06 lb(US))
Returnability	Yes
Country of origin	MX

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds which is known to the State of California to cause Carcinogen & Reproductive harm. For more information go to www.p65warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)

Contractual warranty

Warranty	18 months
----------	-----------