

# 70-150 kW 60Hz

**GENERAC®**

## QT SERIES

Automatic Standby **Gaseous** Generator



Premium Automatic Backup Power for Your Home and Business

# 70-150 kW 60Hz QT SERIES

## AUTOMATIC STANDBY GASEOUS GENERATOR



### Empower your life with the leading choice in standby power.

From business buildings to residential homes, Generac automatic standby generators are being used to provide backup power to a variety of unique applications. Generac's automatic standby generators come on within seconds of a utility power outage to power your electrical loads, ensure your safety, and prevent the loss of revenue or valuable assets. Generac offers an extensive dealer network to provide you with service and maintenance; giving you the confidence you deserve in your generator investment. Choose Generac, the number 1 choice in automatic backup protection, and give yourself peace of mind for years to come.

### Features



**Mobile Link™ Remote Monitoring** allows you to monitor the status of your generator from anywhere in the world using a smartphone, tablet, or PC. Easily access information, such as the current operating status and the generator's maintenance schedule. Connect your account to your authorized service dealer for fast, friendly and convenient assistance. (Sold Separately).



**Assembled in the USA** using domestic & foreign parts



**Quiet-Test™ Self-Test Mode** runs at a lower RPM for a five or twelve minute test, making generators significantly quieter than other brands while consuming less fuel.



**2 Year Limited Warranty**



**24/7•365 Customer Support Team** standing by all day, every day from our headquarters in Wisconsin to answer any questions you might have



**Tough, Durable All-Aluminum Enclosures:** Our RhinoCoat™ powder-coated finish helps make corrosion-resistant aluminum perfect for all weather conditions

SPECIFICATIONS	70 kW	80 kW	100 kW	130 kW	150 kW
Model Number	QT070	QT080	QT100	QT130	QT150
Output Amperage LP/NG 120/240 V, 1ϕ 1.0 pf	292/267	333/333	417/371	542/488	625/567
Output Amperage LP/NG 120/208 V, 3ϕ 0.8 pf	243/232	278/278	347/326	451/423	520/493
Output Amperage LP/NG 120/240 V, 3ϕ 0.8 pf	211/201	241/240	301/283	391/367	451/427
Output Amperage LP/NG 277/480 V, 3ϕ 0.8 pf	105/101	120/120	150/141	195/183	225/214
Engine Alternator RPM	1800	3600	2300	2970	3600
Engine	V-Type 10-Cyl.	V-Type 8-Cyl.	V-Type 10-Cyl.		
Fuel Consumption @ full load - LPG Ft <sup>3</sup> /hr (gal/hr)	411 (11.1)	465 (15.7)	507 (13.9)	719 (19.8)	830 (22.6)
Fuel Consumption @ full load - NG Ft <sup>3</sup> /hr	1020	1252	1260	1786	2061
dB(A) at exercise	64	65	68	69	66
dB(A) at normal operating load	72	74	72	75	79
Automatic Transfer Switch	Not Included				
Enclosure	Aluminum				
Enclosure Color	Bisque				
Warranty	2-Year Limited				
Dimensions L" x W" x H" (in)	96.5" x 36.9" x 47.9"	115.2" x 36.8" x 59.9"	115.2" x 36.8" x 61.9"		
Weight (lbs.)	2040	2035	2531	2699	2492
SCAQMD Model	•		•	•	•

### Nationwide Dealer Service Network

Generac's commitment to service includes scheduled maintenance programs, warranty assistance and emergency service to ensure that Generac customers are never left powerless. The largest nationwide dealer network has factory-trained technicians on staff and maintains large inventories of Generac parts, components and accessories. Find a dealer near you at [generac.com](http://generac.com).

