

XVC6B3

Harmony XVC, Monolithic precabled tower light, plastic, red orange green, Ø60, tube mounting, steady, IP23, 24 V AC/DC



Main

Range of Product	Harmony XVC6
Product or Component Type	Complete pre-wired monolithic tower light
Beacon or indicator bank unit type	3 illuminated units
Sound signalling	Without
Mounting diameter	2.36 in (60 mm)
Component name	XVC
Light source	LED steady red LED steady orange LED steady green
[Us] rated supply voltage	24 V
Supply circuit type	AC/DC

Complementary

Material	Polycarbonate illuminated unit ABS (acrylonitrile butadiene-styrene) base unit PBT + ABS (UL94HB) top cover STK (chromium-plated) support tube
Product mounting	On support tube, 22 mm
Cable cross section	0.00 in ² (0.33 mm ²)
AWG gauge	AWG 22
Cable length	23.62 in (600 mm)
Marking	CE
[Uimp] rated impulse withstand voltage	0.8 kV
Current Consumption	75 mA
Flashing frequency	1 Hz
Net Weight	1.72 lb(US) (0.78 kg)
Height	20.01 in (508.3 mm)

Environment

Standards	EN/IEC 61000-6-4 EN/IEC 61000-6-2 EN/IEC 61000-6-3
Product Certifications	UL
Protective treatment	TC
Ambient Air Temperature for Storage	-31...158 °F (-35...70 °C)
Ambient air temperature for operation	14...122 °F (-10...50 °C)
Electrical shock protection class	Class I EN/IEC 61140
IP degree of protection	IP23 vertical surface installation EN/IEC 60529

Ordering and shipping details

Category	22617 - XVC TOWER LIGHTS
Discount Schedule	XV
GTIN	3606480032561
Nbr. of units in pkg.	1
Package weight(Lbs)	2.31 lb(US) (1.048 kg)

Returnability	Yes
Country of origin	ID

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	3.43 in (8.7 cm)
Package 1 width	3.35 in (8.5 cm)
Package 1 Length	30.51 in (77.5 cm)
Unit Type of Package 2	S06
Number of Units in Package 2	1
Package 2 Weight	28.66 lb(US) (13 kg)
Package 2 Height	28.94 in (73.5 cm)
Package 2 width	23.62 in (60 cm)
Package 2 Length	31.50 in (80 cm)
Unit Type of Package 3	P06
Number of Units in Package 3	20
Package 3 Weight	71.08 lb(US) (32.242 kg)
Package 3 Height	30.31 in (77 cm)
Package 3 width	31.50 in (80 cm)
Package 3 Length	23.62 in (60 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------

Pre-assembled and Pre-wired Tower Light

Support Tube Mounting

