



T5 Light Fixtures & Lamps for Paint Booths

SPECIFICATIONS

An upgrade option on most GFS paint booths and finishing equipment, T5 light fixtures are recommended for tall booths or booths located in areas that reach high temperatures. GFS T5 light fixtures and lamps offer excellent performance and efficiency.



T5 FIXTURE FEATURES

- High output, energy-efficient T5, 54 watt electric ballast
- ETL and ETL-C listed
- Environmentally responsible*
- Enclosed and gasketed construction
- Twist-In lamp holders
- Inside access
- Interlock safety switch
- Easy lamp replacement and retrofits
- Template for installation into existing panels

*when used with low mercury tube

CLASS 1, DIVISION II - GROUPS A, B, C & D

These light fixtures were designed for locations in which volatile flammable liquids or gases are handled, processed or used. For an exceptional spraying environment, choose from six-tube or four-tube, tubes are included.

Fixture Models		Hertz	Voltage Range	Dual Input Amps		Fixture Dimensions (Height X Width) Inches		
Four-Tube	Six-Tube			Four-Tube	Six-Tube	Fixture*	Lens	Panel Opening
LABW-I4T5-D12	LABW-I6T5-D12	50/60	120 - 277	2.00/0.86	3.04/1.32	18.5 x 51.538	18.876 x 52.118	18 x 50.25
LAR-I4T5-D12	LAR-I6T5-D12					21.684 x 50.837	26.898 x 52.399	24.812 x 50.223

* Dimensions are approximate

T5 LAMP



T5 lamps are environmentally-responsible, ultra-slim and have extraordinary light output and longer life.

GFS Part No:	Watt	Color Temperature	Brightness	CRI
230-285	54	5000K	5000 Lumens	85