

# Product data sheet

## Characteristics

# 8910DPA33V02

Contactor, Definite Purpose, 30A, 3 pole, 20 HP at 575 VAC, 3 phase, 110/120 VAC 50/60 Hz coil, open



### Main

Product or Component Type	Definite Purpose Contactor
Line Rated Current	30 A
Number of Poles	3P
Pole contact composition	3 NO
Range of Product	DPA

### Complementary

Maximum Horse Power Rating	2 Hp 115 V AC, 1 phase 5 Hp 230 V AC, 1 phase 10 Hp 230 V AC, 3 phase 15 Hp 460 V AC, 3 phase 20 hp 575 V AC, 3 phase
Locked rotor rated current	150 A 460 V AC 120 A 575 V AC 180 A 277 V AC
[Ue] rated operational voltage	600 V AC
[Uc] control circuit voltage	120 V AC 60 Hz 110 V AC 50 Hz
Phase	3 phase
Electrical Connection	Binder head Quick connect terminals
Height	2.31 In (58.67 mm) 2.31 in (58.70 mm)
Width	2.37 In (60.20 mm) 2.37 in (60.2 mm)
Depth	2.90 In (73.66 mm) 2.99 in (76 mm)
Net Weight	0.99 Lb(US) (0.45 kg) 0.99 lb(US) (0.45 kg)

### Environment

Product Certifications	UL Recognized CSA
------------------------	----------------------

### Ordering and shipping details

Category	21343 - 8910 DPA 3_(30 AMP)
Discount Schedule	CP1B
GTIN	785901073536
Nbr. of units in pkg.	1
Package weight(Lbs)	15.84 oz (449.056 g)
Returnability	Yes
Country of origin	CN

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	3.10 in (7.874 cm)
Package 1 width	2.50 in (6.35 cm)
Package 1 Length	4.00 in (10.16 cm)

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

## Contractual warranty

Warranty	18 months
----------	-----------

Approximate Dimensions

