




ITEM NO.	DESCRIPTION	QTY.
1	PLATE, FLUSH, 4P, W/LABELS	1
2	SCREW, 6-32 PAN HD-SPECIAL	2
3	CARD, PAPER, 40X1.92, BLANK	2
4	COVER LABEL, CLEAR	2
5	COVER LABEL, MATCHING COLOR	2



CATALOG NUMBER	COLOR	DESCRIPTION
IFP140W	OFFICE WHITE	PLATE, FLUSH 4 PORT
IFP14EI	ELECTRIC IVORY	PLATE, FLUSH 4 PORT
IFP14W	WHITE	PLATE, FLUSH 4 PORT
IFP14GY	GRAY	PLATE, FLUSH 4 PORT
IFP14TI	TELCO IVORY	PLATE, FLUSH 4 PORT
IFP14BK	BLACK	PLATE, FLUSH 4 PORT
IFP14AL	ALMOND	PLATE, FLUSH 4 PORT
IFP14LA	LIGHT ALMOND	PLATE, FLUSH 4 PORT
IFP14BN	BROWN	PLATE, FLUSH 4 PORT



NOTES  
UNLESS OTHERWISE SPECIFIED:

1. UL LISTED: E129878
2. CSA CERTIFIED: LR 80837
3. SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE

REV.	ECN	DATE	DESCRIPTION	CHG BY	APPD BY
D	16450	7/7/10	ADDED BROWN COLOR	CG	

Created on AUTOCAD

DIMENSIONING AND TOLERANCE PER ANSI Y14.5M-1982  
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES (MM).  
TOLERANCES:  
.XX = ±.01 (.25)  
.XXX = ±.005 (.127)  
.XXXX = ±.0025 (.0635)  
ANGLE TOL ±1°

IN ACCEPTING OUR DRAWINGS, BLUEPRINTS, OR SUPPORTING DOCUMENTATION FOR QUOTATION OR OTHER PURPOSES, YOU AGREE NOT TO DISCLOSE TO OTHERS THE IDEAS, INFORMATION, OR DESIGNS SHOWN HEREIN, AND THAT YOU WILL MAKE NO USE OF SAME WITHOUT PERMISSION

PROJECT REFERENCE:  
MATERIAL:  
DRAWN BY: P.S. MAGUIRE 02/22/2001  
CHECKED BY: H. MCGREGOR 02/28/2001  
APPROVED BY: H. MCGREGOR 02/28/2001

TITLE: **HUBBELL** INFINE STATION FACE PLATE  
FLUSH 4-PORT WITH LABEL HOLDERS  
14 Lord's Hill Road, Stonington, Connecticut 06378  
Hubbell Premise Wiring  
HUBBELL INCORPORATED (Delaware)

SIZE: C DRAWING NO.: C773066  
SCALE: FULL SHEET 1 OF 1