



YA Series

Pocket Scale



Convenient and portable weighing capability in the palm of your hand!

The OHAUS YA Series Pocket Scale delivers great performance in a stylish, yet functional design and convenient size, that's ideal to take anywhere – carry it in a brief case or drop it in your pocket! With a bright, backlit LCD and simple, quick operation, it puts precision weighing in the palm of your hand!

Standard Features Include:

- Unique hinged cover design protects the scale
- Rugged plastic construction with stainless steel weighing pan
- Weighs in g, oz, ct, gn, dwt
- Energy-saving auto shut-off feature

YA Series Pocket Scale

Specifications

Model	YA102	YA302	YA501
Capacity	100g	300g	500g
Readability	0.01g	0.05g	0.1g
Linearity	± 3 d		
Repeatability	± 3 d	± 3 d	± 3 d
Weighing Units	g, oz, ct, gn		
Operating Temperature Range	50°F - 77°F / 10°C - 25°C		
Power Requirements	2 'AAA' batteries (included)		
Scale Dimensions	4.3 2.9 x 0.79 in / 110 x 75 x 20 mm		
Pan Size	2.76 x 1.97 in / 70 x 50 mm		
Package Dimensions	5.9 x 3.94 x 1.18 in / 150 x 100 x 30 mm		

Standard Features

High contrast LCD, stainless steel weighing pan, hinged pan cover, low battery indicator, auto shut-off, 2-AAA batteries.

Industry Leading Quality and Support

All OHAUS YA Scales are manufactured under an ISO 9001:2008 Registered Quality Management System.

Our rugged construction and stringent quality control have been hallmarks of all OHAUS products for over a century.



OHAUS CORPORATION

* 7 Campus Drive
Suite 310
Parsippany, NJ 07054 USA

Tel: 800.672.7722
973.377.9000
Fax: 973.944.7177

www.ohaus.com

*With offices throughout Europe,
Asia, and Latin America*

* ISO 9001
Registered Quality Management System

80774592 © Copyright Ohaus Corporation

