Straight Blade Devices 15A, 125V, 2 Pole, 3 Wire Grounding **HBL® Extra Heavy Duty Specification** Grade Single Receptacle

HUBBELL

Features

- One-piece brass integral ground strap
- Unique bypass contact design

Ordering Information

Description	Device Color	UPC	Catalog Number
Back and side wired	lvory	783585014166	HBL5261I

Listings

UL Listed to UL498 File No. E2186 Certified to CSA 22.2, No. 42 File 285

Fed. Spec. W-C-596 NEMA® WD-6 Compliant

Specifications

Face Nylon Base **PBT**

Power Contacts .037 in. (.9) Brass

Ground Contact Brass

.050" (1.3) Brass Mounting Strap Auto Self-grounding Clip Stainless steel Mounting Screws Zinc plated steel

Performance

Electrical

Current Interrupting Certified for current interrupting at full rated current Dielectric Voltage

Withstands 2,000V minimum

Mechanical

Ratings are a permanent part of the device **Product Identification**


#14-#10 AWG copper stranded or solid conductor only **Terminal Accommodation** Terminal Identification Terminals identified in accordance with UL 498 and CSA

Environmental

Flammability Top: UL 94V-2, Base: UL 94V-0

Operating Temperatures Maximum continuous 75°C; minimum -40°C (w/o impact)





Accessories

Wallplate or Weatherproof Cover 1.40" Opening

Resources

Customer Use Drawing eCatalog

