

BUILT TO BE **TOUGH**. MADE TO BE **EASY**.



# Scout 6

## Walk-Behind Cordless Sweeper

### Durable Battery-Powered Walk-Behind Sweeper

Easily and quietly clean hard floor and carpet with the Scout 6 maneuverable, cordless walk-behind sweeper.



**Operate easily** with ergonomic controls, dual down pressure settings and filter shaker activation



**Clean efficiently** with wide cleaning path, large hopper capacity, and up to 2 hour run time on one charge.



**Protect your investment** with field-proven durable construction and components.

# Inside the **Scout 6**

- 1. Seamlessly transition from hard to soft floor** cleaning with automatic main brush adjustment.
- 2. Clean anytime, anywhere** with cord-free operation and low dBa.
- 3. Quiet operation** with excellent dust control for noise and dust sensitive environments.



## Scout 6 Specifications

FEATURE	SPECIFICATION
Cleaning path	25 in / 635 mm
Productivity (per hour) Theoretical Max*	18,750 ft <sup>2</sup> / 1,742 m <sup>2</sup>
Productivity (per hour) Practical Max*	18,000 ft <sup>2</sup> / 1,672 m <sup>2</sup>
Hopper capacity	1.25 ft <sup>3</sup> / 35 L
Battery type	Gel 42Ah / C20
Battery run time (up to hours)**	2 hours
Charger - On board	12 V
Filtration	99.5% efficient for particles up to 2 microns
Length x width x height	34 x 28 x 42 in / 870 x 700 x 1,067 mm
Weight (with batteries)	115 lbs / 53 Kg
Sound level (operator's ear)***	61 dBA

*Specifications subject to change without notice and will vary throughout the operation of the machine; averages are shown.  
 \*Standards from the ISSA 612 Cleaning Times handbook.  
 \*\*Run times are based on surface type/brush down pressure.  
 \*\*\*Sound level is measured as an A-weighted sound pressure level per ISO 11201.*