

BUILT TO BE **TOUGH**. MADE TO BE **EASY**.



Scout 7

Wide-Area Cordless Sweeper

Durable Battery-Powered Walk-Behind Sweeper

Easily and quietly clean hard floor and carpet with the Scout 7 maneuverable, cordless walk-behind sweeper.



Quiet with excellent dust control for noise and dust sensitive environments.



Extremely efficient - clean up to 3 hours with one charge. Plus, extra wide cleaning path with side broom hopper capacity.



Comfortable to use with traction control and on-board charger for convenient charging anywhere.

Inside the **Scout 7**

1. Easy to use and understand console

ensures successful operation and performance.

2. Outstanding filtration

with pre-filter and filter with self-cleaning ensures dust free operation.

3. Large debris hopper

ensures productivity and engagement of flap trap allows the capture of larger debris.



Scout 7 Specifications

FEATURE	SPECIFICATION
Cleaning path	28 in / 700 mm
Productivity (per hour) Theoretical Max	28,000 ft ² / 2,601 m ²
Estimated Coverage* Practical	27,000 ft ² / 2,508 m ²
Hopper capacity	1.6 ft ³ / 45 L
Battery type	Gel / 12 Volt
Battery power	12 V 140 AH
Battery run time (up to hours)**	3 hours
Charger type	on board
Filtration	99.5% efficient for particles up to 5 microns
Length x width x height	49 x 29 x 37.75 in / 1,245 x 740 x 960 mm
Weight (with batteries)	267 lbs / 121 kg
Sound level (operator's ear)***	70 dBA

*Specifications subject to change without notice and will vary throughout the operation of the machine; averages are shown.
*Standards from the ISSA 612 Cleaning Times handbook.
**Run times are based on surface type/brush down pressure.
***Sound level is measured as an A-weighted sound pressure level per ISO 11201.*