



Elastic cuff with Velcro® closure for a secure fit

Pull tab loop

Grip in dry or light oil situations

MudGrip+ palm: Synthetic leather with abrasion resistant PVC dots

Back-of-hand sewn-on IR-X® Impact Exoskeleton™ with high-flex design provides ANSI/ISEA 138 Level 2 protection on knuckles and fingers

Reinforced TP-X® index finger and thumb saddle

Woven liner provides industry-leading cut resistance on palm and around top of thumb and index finger (interior layer)

High dexterity

Reinforced seams

Form-fitting, quality materials

Launderable

Hi-vis color scheme



2028X

Rig Lizard® Mud Grip+®

PROTECTION ZONES:

	Impact Protection		TP-X® Technology		Woven Liner
ANSI/ISEA CUT		GRAM SCORE			
A6		3472			
ANSI/ISEA 138		ANSI/ISEA PUNCTURE			
2		4			
CE		EN407 Contact Heat		LEVEL 2	
3X43EP					

FEATURES:

The Rig Lizard® Series is purpose-built to provide maximum grip in tough situations – with over five grip options for water, oils, muds, and lubricants. Each glove is also equipped with our highly flexible IR-X® Impact Exoskeleton™, keeping hands protected from smash and pinch injuries. This combination of multiple technologies and features makes the Rig Lizard® the ideal solution for common oil, gas, and mining hazards. With options for cold weather protection, your hands can stay safe and comfortable in any environment.

ATTRIBUTES:

Style:	Mechanics
Grip:	Dry or Light Oil
Cuff Style:	Elastic with Velcro® closure
Sizes:	6/XS through 12/XXXL

HexArmor®

Call 1-877-MY ARMOR or visit hexarmor.com

HexArmor® products are cut and puncture resistant, NOT CUT AND PUNCTURE PROOF. Do not use with moving or serrated blades or tools. User shall be exclusively responsible to assess the suitability of the product as specified for any individual application or use. Protection zones are to be used as a general guide. Actual product protection zones may differ. Product features, design, protection zones subject to change.

Protected by U.S. Patent No. D703,389