



SUPER DUTY NITRILE

SPEC SHEET

SPECIFICATIONS	
TENSILE STRENGTH (Min. Mpa) Before Aging : 14 Mpa After Aging : 14 Mpa	3 SIZES (M,L ,XL) For a comfortable fit.
ELASTICITY/ELONGATION (%) Before Aging : 500% After Aging : 400%	LATEX FREE Nitrile gloves are a latex free solution for professionals concerned with latex sensitivity.
PROTEIN CONTENT N/A	TEXTURED/MICRO-ROUGHENED For a superior wet or dry grip.
AVG. MIN. POWDER MASS (Min. mg Per Glove) <2 mg	POWDER-FREE Avoids interference with adhesives and inks.
AQL LEVEL : 4.0	
SUPERB TENSILE STRENGTH Beaded cuff for increased tear resistance.	
NITRILE WARNING: Components used in making nitrile gloves may cause allergic reactions in certain individuals.	
100 individual gloves by weight	

COLOR	
ORANGE	
PART NUMBERS	
D01-09-009-100 (M)	
D01-09-010-100 (L)	
D01-09-011-100 (XL)	
UPC CODES	
D01-09-009-100 (M)	
EACH	781513654996
MASTER	70781513654995
D01-09-010-100 (L)	
EACH	781513655009
MASTER	70781513655008
D01-09-011-100 (XL)	
EACH	781513655016
MASTER	70781513655015
10 BOXES PER MASTER CASE	



THICKNESS



LATEX FREE



POWDER FREE



DIAMOND TEXTURE



*Prices and Quantities
Subject to Change*